

The powerful and handy high-pressure washer for basic use with powercontrol

This elegant Nilfisk high pressure washer with power control for adjustable water pressure easily handles your cleaning tasks.

The long life metal pump provides the power to clean everything from soft and sensitive surfaces to blasting away ingrained dirt up to 35 m²/hour.






With the ultraflex hose cleaning tasks are no hassle and the hose pocket helps easy stow away.

- 130 max pressure
- Long life metal pump
- Cleaning speed index: 35
- Automatic start/stop system
- Gentle & Rough nozzles system with user guidance
- Trolley for high mobility
- Click&Clean connectivity for quick and easy change of accessories
- Hose Pocket
- Quick Connect
- 6m Ultraflex hose
- Nozzle user guide
- Power Control










Picture shown may not represent model quoted

• Standard equipment

Included accessories		Ref. no.	Min. required	CORE 130-6 POWERCONTROL - UK
Hose and Connection				
	G1 GUN NILFISK	128500908	0	•
Nozzle - High Pressure Washer				
	C&C GENTLE NOZZLE (TORNADO)	128500076	0	•
	C&C ROUGH NOZZLE (POWERSPEED)	128501153	0	•
	Wide Angled Auto & Cycle Nozzle	6411136	0	
Brush				
	Auto Brush	6411131	0	



The powerful and handy high-pressure washer for basic use with powercontrol

Included accessories		Ref. no.	Min. required	CORE 130-6 POWERCONTROL - UK
	FIXED BRUSH SHORT NILFISK SP	128500685	0	
Accessory				
	C&C FOAMSPRAYER WITH BOTTLE	128500077	0	•
	Compact Patio	128500700	0	
	DRAIN AND TUBE 8M	128500461	0	
	G2 C&C SPRAY LANCE	128500073	0	•
	NILFISK C&C SUPER FOAM SPRAYER	128500938	0	
	Patio Cleaner	128500702	0	

Model CORE 130-6
POWERCONTROL
- UK

Ref. no. 128471286

PRODUCT FEATURES

Trolley	•
Hose reel	
Aluminium pump	•
Lance and spray gun storage	•
Storage of accessories	•
Cable storage	•
Click&Clean (C&C) nozzle concept	•
Gun with quick connection and swivel	•
Automatic start/stop	•



The powerful and handy high-pressure washer for basic use with powercontrol

Model	CORE 130-6 POWERCONTROL - UK
Ref. no.	128471286

PRODUCT FEATURES

Soft grip
Hose and cable holder
Telescopic handle
Wireless PowerGrip
Pressure regulation in nozzle





•

Technical specifications

Pump pressure (bar/MPa)	Max 130 / max 13
Rated power (kW)	1,5
Voltage/phase/frequency/current (V~/Hz/A)	220 - 240 / 1~/ 50-60 / 6.5
Water flow Qmax/Qiec (l/h)	462 / 324
Cable length (m)	5
Hose length (m)	6
Max. inlet temperature (°C)	40
Length x width x height (cm)	
Weight (kg)	6,6












CORE 130-6
POWERCONTROL
- UK

• Standard equipment, ◊ Supplementary accessories, □ Mountable equipment

Accessories		Ref. no.	Min. required	CORE 130-6 POWERCONTROL - UK
Hose and Connection				
	7m Extension high pressure hose with quick coupling	6410760	0	◊
	EXT. HOSE 7 M - QUICK COUPLING	106411346	0	◊
	EXTENSION HOSE STEEL ARMED 7 M	6411048	0	◊
	G1 GUN NILFISK	128500908	0	•















The powerful and handy high-pressure washer for basic use with powercontrol

Accessories		Ref. no.	Min. required	CORE 130-6 POWERCONTROL - UK
	NILFISK BA VALVE COMP. GARDENA	106411177	0	○
Brush				
	Auto Brush	6411131	0	○
	CAR BRUSH HEAD	128500463	0	○
	FIXED BRUSH SHORT NILFISK SP	128500685	0	○
	GARDEN BRUSH HEAD	128470457	0	○
	RIM BRUSH HEAD	128470458	0	○
	Rotary Brush	126411395	0	○
	ROTARY BRUSH	6410762	0	○
Accessory				
	C&C FOAMSPRAYER WITH BOTTLE	128500077	0	●
	CLEANING TOOL BLACK	6520844	0	○
	Compact Patio	128500700	0	○













The powerful and handy high-pressure washer for basic use with powercontrol

	Accessories	Ref. no.	Min. required	CORE 130-6 POWERCONTROL - UK
	DRAIN AND TUBE 8M	128500461	0	○
	DRAIN AND TUBE CLEANER 15M	6410766	0	○
	G2 C&C SPRAY LANCE	128500073	0	●
	INLET SUCTION HOSE 3M	128500673	0	○
	MULTI ANGLE ADAPTER	6411138	0	○
	MULTI BRUSH	128470456	0	○
	NILFISK C&C SUPER FOAM SPRAYER	128500938	0	○
	NILFISK POWER PATIO	128500955	0	○
	NILFISK TOWEL	128501316	0	○
	NILFISK WASHING GLOVE	128501317	0	○
	NILFISK WATER FILTER	128500674	0	○
	Patio Cleaner	128500702	0	○



The powerful and handy high-pressure washer for basic use with powercontrol

Accessories		Ref. no.	Min. required	CORE 130-6 POWERCONTROL - UK
	ROOF CLEANER	128470040	0	○
	Under Chassis Spray Lance	6410763	0	○
	VSB SET - GREEN	6410891	0	○
	Water Emptying Kit	126411387	0	○
Nozzle - High Pressure Washer				
	C&C GENTLE NOZZLE (TORNADO)	128500076	0	●
	C&C ROUGH NOZZLE (POWERSPEED)	128501153	0	●
	Wide Angled Auto & Cycle Nozzle	6411136	0	○
Accessory Kit				
	MULTI BRUSH KIT	128470459	0	○
	NILFISK CAR WASH KIT TOWEL WASHING MIT	128501318	0	○
	O-RING KIT CONSUMER HPW	128500292	0	○