

The powerful and easy to handle high-pressure washer for allround use







This powerful Nilfisk high pressure washer with power control for adjustable water pressure easily handles your cleaning tasks. The ultra torque engine and long life metal pump provides the power to clean everything from soft and sensitive surfaces to blasting away ingrained dirt up to 40 m2/hour. With the ultraflex hose cleaning tasks are no hassle and the integrated hose reel makes stow away easy.

- 140 max pressure
- Long life metal pump
- Cleaning speed index: 40
- Automatic start/stop system
- Gentle & Rough nozzles system with user guidance
- Trolley for high mobility
- Click&Clean connectivity for quick and easy change of accessories
- Internal Hose reel
- 6m Ultraflex hose
- Nozzle user guide
- Power Control













Picture shown may not represent model quoted

• Standard equipment

| Included accessories | | Ref. no. | Min. required | CORE 140-6 POWERCONTROL UK |
|---|---------------------------------|-----------|---------------|----------------------------|
| Nozzle - High Pressure Washer | | | | |
|  | C&C GENTLE NOZZLE (TORNADO) | 128500076 | 0 | • |
|  | C&C ROUGH NOZZLE (POWERSPEED) | 128501153 | 0 | • |
|  | Under Chassis Nozzle | 6411135 | 0 | |
|  | Wide Angled Auto & Cycle Nozzle | 6411136 | 0 | |
| Brush | | | | |
|  | Auto Brush | 6411131 | 0 | |
|  | FIXED BRUSH SHORT NILFISK SP | 128500685 | 0 | |



The powerful and easy to handle high-pressure washer for allround use

| Included accessories | | Ref. no. | Min. required | CORE 140-6 POWERCONTROL UK |
|---|-----------------------------------|-----------|---------------|----------------------------|
| Accessory | | | | |
|  | C&C FOAMSPRAYER WITH BOTTLE | 128500077 | 0 | • |
|  | CLEANING TOOL BLACK | 6520844 | 0 | • |
|  | Compact Patio | 128500700 | 0 | |
|  | DRAIN AND TUBE 8M | 128500461 | 0 | |
|  | G3 GUN WITH INTERMEDIATE TUBE | 126481132 | 0 | • |
|  | G3 LANCE | 126481134 | 0 | • |
| | NILFISK ACCESSORY HOLDER CORE 140 | 128501319 | 0 | |
|  | NILFISK C&C SUPER FOAM SPRAYER | 128500938 | 0 | |
|  | NILFISK TOWEL | 128501316 | 0 | |
|  | NILFISK WASHING GLOVE | 128501317 | 0 | |
|  | Patio Cleaner | 128500702 | 0 | |



The powerful and easy to handle high-pressure washer for allround use


| | |
|----------|----------------------------------|
| Model | CORE 140-6 POWERCONTROL UK |
| Ref. no. | 128471254 |

PRODUCT FEATURES

| | |
|--------------------------------------|---|
| Trolley | • |
| Hose reel | • |
| Aluminium pump | • |
| Lance and spray gun storage | • |
| Storage of accessories | • |
| Cable storage | • |
| Click&Clean (C&C) nozzle concept | • |
| Gun with quick connection and swivel | • |
| Automatic start/stop | • |
| Soft grip | • |
| Hose and cable holder | • |
| Telescopic handle | • |
| Wireless PowerGrip | • |
| Pressure regulation in nozzle | • |












| | |
|--|----------------------------------|
| Technical specifications | CORE 140-6 POWERCONTROL UK |
| Pump pressure (bar/MPa) | Max 140 / max 14 |
| Rated power (kW) | 1,8 |
| Voltage/phase/frequency/current (V/~/Hz/A) | 220 - 240 / 1~/ 50-60 / 7 |
| Water flow Qmax/Qiec (l/h) | 474 / 348 |
| Cable length (m) | 5 |
| Hose length (m) | 6 |
| Max. inlet temperature (°C) | 40 |
| Length x width x height (cm) | 88,2 x 37,1 x 30 |
| Weight (kg) | 8,7 |

● Standard equipment, ○ Supplementary accessories, □ Mountable equipment

| Accessories | | Ref. no. | Min. required | CORE 140-6 POWERCON- TROL UK |
|--|------------|----------|---------------|------------------------------------|
| Brush | | | | |
|  | Auto Brush | 6411131 | 0 | ○ |














The powerful and easy to handle high-pressure washer for allround use

| Accessories | | Ref. no. | Min. required | CORE 140-6 POWERCONTROL UK |
|---|------------------------------|-----------|---------------|----------------------------|
|  | CAR BRUSH HEAD | 128500463 | 0 | ○ |
|  | FIXED BRUSH SHORT NILFISK SP | 128500685 | 0 | ○ |
|  | GARDEN BRUSH HEAD | 128470457 | 0 | ○ |
|  | RIM BRUSH HEAD | 128470458 | 0 | ○ |
|  | Rotary Brush | 126411395 | 0 | ○ |
|  | ROTARY BRUSH | 6410762 | 0 | ○ |
| Accessory | | | | |
|  | C&C FOAMSPRAYER WITH BOTTLE | 128500077 | 0 | ● |
|  | CLEANING TOOL BLACK | 6520844 | 0 | ● |
|  | Compact Patio | 128500700 | 0 | ○ |
|  | DRAIN AND TUBE 8M | 128500461 | 0 | ○ |
|  | DRAIN AND TUBE CLEANER 15M | 6410766 | 0 | ○ |














The powerful and easy to handle high-pressure washer for allround use

| | Accessories | Ref. no. | Min. required | CORE 140-6 POWERCONTROL UK |
|---|-----------------------------------|-----------|---------------|----------------------------|
|  | G3 GUN WITH INTERMEDIATE TUBE | 126481132 | 0 | • |
|  | G3 LANCE | 126481134 | 0 | • |
|  | INLET SUCTION HOSE 3M | 128500673 | 0 | ○ |
|  | MULTI ANGLE ADAPTER | 6411138 | 0 | ○ |
|  | MULTI BRUSH | 128470456 | 0 | ○ |
| | NILFISK ACCESSORY HOLDER CORE 140 | 128501319 | 0 | ○ |
|  | NILFISK C&C SUPER FOAM SPRAYER | 128500938 | 0 | ○ |
|  | NILFISK POWER PATIO | 128500955 | 0 | ○ |
|  | NILFISK TOWEL | 128501316 | 0 | ○ |
|  | NILFISK WASHING GLOVE | 128501317 | 0 | ○ |
|  | NILFISK WATER FILTER | 128500674 | 0 | ○ |
|  | Patio Cleaner | 128500702 | 0 | ○ |





The powerful and easy to handle high-pressure washer for allround use

| Accessories | | Ref. no. | Min. required | CORE 140-6 POWERCONTROL UK |
|---|---------------------------------|-----------|---------------|----------------------------|
|  | ROOF CLEANER | 128470040 | 0 | ○ |
|  | Under Chassis Spray Lance | 6410763 | 0 | ○ |
|  | VSB SET - GREEN | 6410891 | 0 | ○ |
|  | Water Emptying Kit | 126411387 | 0 | ○ |
| Nozzle - High Pressure Washer | | | | |
|  | C&C GENTLE NOZZLE (TORNADO) | 128500076 | 0 | ● |
|  | C&C ROUGH NOZZLE (POWERSPEED) | 128501153 | 0 | ● |
|  | Under Chassis Nozzle | 6411135 | 0 | ○ |
|  | Wide Angled Auto & Cycle Nozzle | 6411136 | 0 | ○ |
| Hose and Connection | | | | |
|  | EXT. HOSE 7 M - QUICK COUPLING | 106411346 | 0 | ○ |
|  | NILFISK BA VALVE COMP. GARDENA | 106411177 | 0 | ○ |
| Accessory Kit | | | | |
|  | MULTI BRUSH KIT | 128470459 | 0 | ○ |



The powerful and easy to handle high-pressure washer for allround use

| Accessories | | Ref. no. | Min. required | CORE 140-6 POWERCONTROL UK |
|--|--|-----------|---------------|----------------------------|
|  | NILFISK CAR WASH KIT TOWEL WASHING MIT | 128501318 | 0 | ○ |
|  | O-RING KIT CONSUMER HPW | 128500292 | 0 | ○ |

