

## SATA to USB Cable with UASP

**Product ID:** USB3S2SAT3CB



This SATA to USB cable is an external drive adapter that gives you quick and easy access to a SATA drive through the USB-A port on a laptop.

This SATA solid-state (SSD) or hard drive (HDD) adapter lets you upgrade to an external 2.5" SATA SSD or HDD.

The cable lets you:

- Add drive space
- Perform backups
- Create disk images
- Implement data recovery
- Transfer content between the drive and the laptop

The cable supports USB 3.0 data transfer speeds of 5Gbps. But, you can experience transfer speeds up to 70% faster than conventional USB 3.0, when connected to a computer that also supports UASP. With UASP you can utilize the full potential of a SATA III SSD or HDD. UASP is supported in Windows 8, Mac OS X (10.8 or above), and Linux.

In testing, UASP performs with a 70% faster read speed and 40% faster write speed over traditional USB 3.0 at peak performance.

At the same peak in testing, UASP also shows an 80% reduction in required processor resources.

The SATA to USB cable is a portable solution that tucks away nicely in a laptop bag -- no external power is required. The cable lets you easily swap between drives with no need to install the drive inside an enclosure. It's plug-and-play and doesn't require drivers.

USB3S2SAT3CB is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Take advantage of USB 3.0 laptops or desktops with UASP for faster transfer speeds
- Back up important data to an external storage device
- Perform a data migration or clone a drive
- Back up important data to an external storage device
- Retrieve data from an old SATA drive
- Upgrade your laptop HDD to an SSD via USB 3.0

### Features

- Access a SATA SSD or HDD from your laptop with this SATA to USB cable
- Supports USB 3.0 data transfer speeds of 5Gbps and is backward compatible with USB 2.0
- Experience 70% faster read speed and 40% fast write speeds with UASP support
- Save setup time with plug-and-play installation
- Connect to external drives anywhere with this SATA to USB adapter -- no power adapter required

---

#### Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 3.0
Bus Type	USB 3.0
Number of Drives	1
Drive Size	2.5in
Compatible Drive Types	SATA
Chipset ID	ASMedia - ASM1153E

---



## Performance

Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
TRIM Support	Yes
4Kn Support	Yes
Type and Rate	SATA III (6 Gbps)
Hardware Raid Supported	No
Max Drive Capacity	Currently tested with up to 2TB 5900 RPM hard drives
General Specifications	Max power of the attached drive is 900 mA
MTBF	1,609,297 Hours

## Connector(s)

Drive Connectors	SATA Data & Power Combo (7+15 pin)
	SATA Power (15 pin)
Host Connectors	USB Type-A (9 pin) USB 3.0 (5 Gbps)

## Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

## Special Notes / Requirements

Note	Cable will work only with 2.5" SATA drives 3.5"/5.25" drives are not supported  Windows 7 and earlier Windows versions do not support TRIM with USB to SATA devices.
------	---

## Power

Power Source	USB-Powered
--------------	-------------

## Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40%-85%RH



---

**Physical  
Characteristics**

Product Length	19.7 in [50.0 cm]
Product Width	1.9 in [49.0 mm]
Product Height	0.4 in [9.0 mm]
Weight of Product	1.5 oz [42.5 g]

---

**Packaging  
Information**

Package Length	7.8 in [19.8 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.4 in [10.0 mm]
Shipping (Package) Weight	2.2 oz [61.0 g]

---

**What's in the  
Box**

Included in Package	USB 3.0 to SATA 2.5" HDD Adapter Cable
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

