

USB 2.0 300 Mbps Mini Wireless-N Network Adapter - 802.11n 2T2R WiFi Adapter

Product ID: USB300WN2X2C



The USB300WN2X2C USB Wireless Network Adapter lets you add 300 Mbps Wireless-N connectivity to your desktop or laptop system through USB 2.0. With a compact, lightweight design, the adapter is extremely portable, and is unobtrusive when connected to your system - you can even leave it connected to your laptop when in a carrying bag, without worrying about damaging the adapter or the host port while on the move.

The USB wireless adapter is capable of data transfer rates up to 300Mbps over a 2.4GHz 802.11n WiFi network (backward compatible with 802.11b/g), through a 2 Transmitter / 2 Receiver antenna design. The adapter also supports security options such as WEP, WPA or WPA2, as well as quick device connection through Wireless Protected Setup (WPS), for a reliable and secure connection.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Add wireless networking capabilities, without having to open up your computer case
- Replace or upgrade an existing WiFi connection to IEEE 802.11n standards
- Connect to a wireless-N network in remote locations where wired connections are unavailable
- Add high-speed WiFi connectivity to support demanding applications such as streaming video, VoIP and network backups

Features

- Extremely compact and lightweight design
- 2 Transmitter/2 Receiver (2x2:2) antenna configuration
- Compliant with IEEE 802.11n standards, with data rates up to 300Mbps
- Backward compatible with 802.11b/g (11/54Mbps respectively)
- Supports WEP (64-128-bit), WPA and WPA2 wireless security
- Supports WMM Quality of Service

Hardware

Warranty	2 Years
Interface	Wireless Ethernet
Bus Type	USB 2.0
Antenna Configuration	2x2:2 (TxR:S)
Industry Standards	IEEE 802.11b, IEEE 802.11g, IEEE 802.11n
Chipset ID	Realtek - RTL8192EU

Performance

Maximum Data Transfer Rate	300 Mbps
Bandwidth	20 / 40MHz
Frequency Range	2.400GHz ~ 2.484GHz
Security Features	WEP Data Encryption WPA and WPA2-PSK Data Encryption TKIP/AES WPA and WPA2 Enterprise Data Encryption

Connector(s)

Connector Type(s)	USB Type-A (4 pin) USB 2.0 Wireless N (IEEE 802.11n)
-------------------	---

Software

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10
------------------	----------------------------------



Windows Server 2003, 2008 R2, 2012, 2016, 2019

Mac OS X 10.6 to 10.14

Linux kernel 2.6.x, 4.4.x to 4.11.x <i>LTS Versions only</i>

Special Notes / Requirements

System and Cable Requirements	Available USB port
-------------------------------	--------------------

Indicators

LED Indicators	Link / Activity
----------------	-----------------

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C ~ 40C (32F ~ 104F)
Storage Temperature	-40C ~ 70C (-40F ~ 158F)
Humidity	10% ~ 90% RH (Non-condensing)

Physical Characteristics

Color	Black
Material	Plastic
Product Length	0.9 in [22.0 mm]
Product Width	0.6 in [16.0 mm]
Product Height	0.2 in [6.0 mm]
Weight of Product	0.1 oz [2.0 g]

Packaging Information

Package Length	5.6 in [14.3 cm]
Package Width	6.7 in [17.1 cm]
Package Height	1.3 in [32.0 mm]
Shipping (Package) Weight	2.3 oz [65.0 g]



**What's in the
Box**

Included in Package	USB Wireless N Adapter
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

