

Mini DisplayPort to HDMI Adapter - mDP to HDMI Adapter Dongle - 1080p - Mini DisplayPort 1.2 to HDMI Monitor/Display - Mini DP to HDMI Video Converter - 12" Long Attached Cable

Product ID: MDP2HDEC



This Mini DisplayPort to HDMI adapter lets you connect your mDP computer to an HDMI, television, projector or monitor.

This Mini DP to HDMI adapter is equipped with an extra-long 12" (30cm) attached cable, providing an extended reach to reduce port and connector strain on 2-in-1 devices or laptops on risers stands.

With support for video resolutions up to 1080p, you'll be surprised at the picture spectacular picture quality this adapter provides. The adapter harnesses the video capabilities built into your mDP connection to deliver every detail in stunning high-definition.

This mDP video adapter is highly portable with a small footprint and lightweight design that's easy to tuck into your laptop bag while commuting between your home, office or traveling for business.

The MDP2HDEC is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Keep the adapter with you while traveling, to connect to any HDMI monitor, projector or television you come across
- Connect your Mini DisplayPort equipped tablet or smartphone to a larger display

Features

- MINI DISPLAYPORT TO HDMI CONVERSION: Mini DisplayPort 1.2 to HDMI adapter connects an mDP equipped

laptop, MacBook or PC to a single HDMI display supporting resolutions up to 1920x1200p or 1080p 60Hz 7.1 ch audio HDCP 1.4

- **EXTRA LONG CABLE:** Mini DisplayPort to HDMI adapter with 12 inch (30cm) attached cable for extended reach to reduce port/connector strain on 2-in-1 devices like Surface Pro (1-6) and laptops on riser stands Compact, portable design
- **WIDE COMPATIBILITY:** Passive Mini DP to HDMI display adapter supports mDP++ source including Thunderbolt 1 & 2 MacBooks, MacBook Air & Mac Mini, Microsoft Surface Pro 1-6, desktops (AMD FirePro/NVidia Quadro), laptops, mini itx computers, Intel NUC & docks
- **DISPLAY COMPATIBILITY:** External video adapter/converter tested for peak performance at 1920x1200p on a range of HDMI monitors, projectors and displays including brands like Dell, Samsung, Asus ProArt, Acer & LG
- **EASY TO USE:** Mini DisplayPort to HDMI dongle supports driverless plug & play setup and is compatible with macOS, Windows 10, Chrome OS and Ubuntu; mDP male to HDMI female

Hardware

Warranty	3 Years
Chipset ID	NXP Semiconductors PTN3361B

Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Supported Resolutions	HDMI: 1920x1200 / 60Hz
Audio Specifications	HDMI - 7.1 Channel Audio

Connector(s)

Connector A	Mini DisplayPort
Connector B	HDMI (19 pin)

Special Notes / Requirements

System and Cable Requirements	DP++ port (DisplayPort ++) required on video card or video source (DVI and HDMI pass-through must be supported)
-------------------------------	--

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10%-85%RH

Physical

Characteristics

Color	Black
Material	Plastic
Cable Length	13.0 in [33.1 cm]
Product Length	15.2 in [38.7 cm]
Product Width	1.0 in [26.5 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	0.8 oz [24.0 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	0.9 oz [25.0 g]

What's in the Box

Included in Package	Mini DisplayPort to HDMI Adapter
---------------------	----------------------------------

****Product appearance and specifications are subject to change without notice.***

