

7-Port Compact USB 3.0 Hub with Built-in Cable

Product ID: ST73007UA



This compact, 7-port USB 3.0 hub is tailored to match the stylish design of your MacBook. It features a sleek, silver sandblasted housing that looks great next to your Apple laptop. And, because the hub is designed with a solid-aluminum casing, it provides the lightweight durability that's ideal for either travel or desktop usage.

This high-quality, Apple style USB hub gives you an easy way to expand your MacBook connectivity. It provides seven USB 3.0 (also known as USB 3.1 Gen 1) hub ports in a compact housing. With more ports, you have more scalability to connect extra USB devices. Plus, you can leave your devices plugged in, so they're ready to use when you need them.

The 7-port USB 3.0 hub offers a silver sandblast finish that provides a unique and stylish appearance, making the hub look as trendy and contemporary as your MacBook, Ultrabook, or laptop.

The hub features a built-in, 98 cm (38 in) cable that is longer than what most traditional hubs offer. The extended-length cable gives you the flexibility to place the hub and your devices exactly where you want them, and it ensures the hub can connect to your laptop or tablet regardless of where the laptop's USB 3.0 port is located.

This compact hub features seven ports with plenty of space between each port, unlike some USB 3.0 hubs that jam multiple ports into a tightly-packed space which makes it difficult to connect multiple devices to adjacent hub ports. With extra port spacing, you can connect devices and cables that have larger connectors, without sacrificing the hub's small footprint design.

The rugged aluminum housing offers dependable protection, so the hub is perfect for travel, such as back-and-forth trips from home to office. Plus, the compact hub takes up minimal space on a desk, so you can use it in hot-desk or BYOD (Bring Your Own Device) environments.

The easy-to-use hub is plug-and-play and hot-swap compatible, so you can install it quickly, with no additional drivers or software required. It includes a power adapter as well, so you can rest assured that you can connect virtually any USB 3.0 peripheral, even devices with high power requirements. Plus, you can also avoid the nuisance and cost of purchasing new devices by using the USB 3.0 hub with your current USB 2.0 and 1.x devices.

The ST73007UA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Flexible hub placement options with an extended-length cable, so you can connect a wide variety of peripherals at home or in the office
- Carry the hub with you while traveling, and connect virtually any USB peripheral wherever you go
- Deploy in hot-desk environments to provide USB hub access for multiple devices

Features

- Sleek and stylish, with a silver, sandblasted finish that matches your MacBook
- Rear port orientation for better USB device management and less clutter
- Place the hub exactly where you need it, with a compact and lightweight casing, and an integrated, extended-length cable
- Rugged, aluminum housing delivers reliable performance
- SuperSpeed USB throughput support up to 5Gbps
- Connect and operate USB 3.0 devices that require additional power, using the included 20W power adapter
- Backward compatibility lets you save money by using the hub with existing USB 2.0 and 1.x devices
- Plug-and-play and hot-swap compatible
- Provides overcurrent protection

Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	No
Ports	7
Interface	USB 3.0
Bus Type	USB 3.0



Industry Standards USB 3.0 - Backward compatible with USB 2.0/1.1

Chipset ID Genesys Logic - GL3523

Performance

Maximum Data Transfer Rate 5 Gbps

Type and Rate USB 3.0 - 5 Gbit/s

Connector(s)

Connector Type(s) USB Type-A (9 pin) USB 3.0 (5 Gbps)
USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software

OS Compatibility OS Independent; No additional drivers or software required

Special Notes / Requirements

System and Cable Requirements Host computer with a USB 3.0 port

Note If connected to a USB 2.0 host port, performance may be limited

Indicators

LED Indicators Power

Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Input Current 0.6 A

Output Voltage 5 DC


Output Current 4 A

Center Tip Polarity Positive

Plug Type H

Power Consumption (In Watts) 20

Environmental



Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%~90% RH (Non-condensing)

Physical Characteristics

Color	Silver & White
Form Factor	Desktop
Material	Aluminum and Plastic
Cable Length	38.6 in [98 cm]
Product Length	7.2 in [18.3 cm]
Product Width	1.5 in [37 mm]
Product Height	0.7 in [18 mm]
Weight of Product	4.3 oz [122 g]

Packaging Information

Package Length	4.6 in [11.6 cm]
Package Width	9.0 in [22.9 cm]
Package Height	2.3 in [58 mm]
Shipping (Package) Weight	16.6 oz [471 g]

What's in the Box

Included in Package	7-port USB 3.0 hub - compact with built-in cable universal power adapter (NA/EU/UK/AU)
---------------------	---

****Product appearance and specifications are subject to change without notice.***

