

1m USB A to USB C Charging Cable - Durable Fast Charge & Sync USB 2.0 to USB Type C Data Cord - Rugged TPE Jacket Aramid Fiber M/M 3A White - Samsung S10, iPad Pro, Pixel

Product ID: RUSB2AC1MW



This USB C cable withstands the daily demands of charging and syncing your mobile devices. Compatible with your Thunderbolt 3 ports, this rugged cable is a must-have for both business and consumer applications.

The durable USB C charging cable has aramid fiber reinforcement that shelters it from the stress of frequent bends. This also lets the cable flex without over-stretching or damaging the core of the cable.

- Aramid fiber adds strength and durability to the cable
- Insulated conductors reduce friction, provide more flexibility
- EMI (electromagnetic interference) protection with aluminum-mylar foil with braided shielding
- TPE (thermoplastic elastomer) cable jacket is more flexible than a standard PVC cable

The USB A to USB C cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle.

- USB Type C connector provides 3A of power output for charging your USB C compatible devices
- Metal shield protects circuit board from EMI and reinforces the connection point
- Strain relief tested to tolerate over 10,000+ bend cycles at a 180 angle

The durable cable supports all USB 2.0 specifications providing a dependable connection for all your USB-C devices. It also delivers up to 60W of power to charge your devices without needing an additional power supply.

RUSB2CC1MW is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Note: DuPont and Kevlar are trademarks or registered trademarks of E.I. du Pont de Nemours and Company.

Certifications, Reports and Compatibility

Applications

- Charge and sync your USB Type C mobile devices

Features

- **DURABLE:** USB A to USB C charging cable reinforced w/ Kevlar aramid fiber for increased tensile strength 5x stronger than steel. Tested to withstand 10000+ bend cycles at 180 angle & 5000+ insertions
- **SPECS:** Length: 1m (3ft) Color: White Connectors: USB-C to USB-A Performance: USB 2.0 Material: Aramid Fiber Power: 3A Jacket Type: TPE Shielding: EMI Protection
- **USB-C COMPATIBILITY:** Rugged data transfer cable allows you to charge and sync your USB Type C devices including your iPad Pro, Samsung Galaxy S8, S9, S10, S20, S20+, One Plus & Google Pixel 3a, 3, 4 series
- **FAST CHARGE AND SYNC :** Supporting up to 3A for fast charging from a USB-A port or Quick Charge power adapter, this high quality cord is designed to charge and sync your USB C devices
- **FLEXIBLE CABLE:** Built with a TPE jacket to absorb the stress of frequent bends without damaging the core of the cable. TPE is non-toxic, halogen free & RoHS certified for environmental sustainability

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	USB Type-C (24-pin) USB 2.0 (480Mbps)

Physical Characteristics

Color	White
-------	-------

Connector Style	Straight
Wire Gauge	22/32 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100.0 cm]
Product Width	0.6 in [14 mm]
Product Height	0.3 in [7 mm]
Weight of Product	0.9 oz [25 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	1.1 oz [30 g]

What's in the Box

Included in Package	USB-A to USB-C Cable
---------------------	----------------------

****Product appearance and specifications are subject to change without notice.***

