


**Data sheet | Item number: 216-266**

Ferrule; Sleeve for 2.5 mm<sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue



[www.wago.com/216-266](http://www.wago.com/216-266)



Subject to changes. Please also observe the further product documentation!

WAGO Corporation  
Germantown, WI 53022  
Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222  
Email: [info.us@wago.com](mailto:info.us@wago.com) | Web: [www.wago.us](http://www.wago.us)

Do you have any questions about our products?  
We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.



## Data

### Technical data

Main product function	Ferrule
Sleeve cross-section (AWG)	14 AWG
Sleeve for	2.5 mm <sup>2</sup>

### Connection data

Strip length	14 mm / 0.55 inch
--------------	-------------------

### Physical data

Length	19 mm
Length 1	12 mm
Diameter	4.7 mm
Diameter 1	4.2 mm
Diameter 2	2.2 mm

### Mechanical data

Suitable	2002 to 2006 Series
----------	---------------------

### Material data

Color	blue
Fire load	0.002 MJ
Weight	0.2 g

### Commercial data

Product Group	2 (Terminal Block Accessories)
Packaging type	box
Country of origin	DE
GTIN	4044918604314
Customs tariff number	8536904000

## Downloads

### Documentation

#### Bid Text

Subject to changes. Please also observe the further product documentation!

WAGO Corporation  
Germantown, WI 53022  
Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222  
Email: [info.us@wago.com](mailto:info.us@wago.com) | Web: [www.wago.us](http://www.wago.us)

Do you have any questions about our products?  
We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.


216-266 doc - Datei	11 Sep 2017	doc 24.6 kB	Download
216-266 X81 - Datei	19 Feb 2019	xml 2.9 kB	Download

## Environmental Product Compliance

### Compliance Search

Environmental Product Compliance 216-266 Ferrule; Sleeve for 2.5 mm <sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue	URL	Download
---	-----	----------

## Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable

Subject to changes. Please also observe the further product documentation!