



# CorePro LEDcapsule LV

## CorePro LEDcapsuleLV 1-10W G4 827

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

### Product data

General Information		Operating and Electrical	
Cap base	G4 [ G4]	Input frequency	- Hz
EU RoHS compliant	Yes	Power (Rated) (Nom)	1 W
Nominal lifetime (nom.)	15000 h	Lamp current (nom.)	138 mA
Switching cycle	50,000X	Wattage equivalent	10 W
Technical type	1-10W	Starting time (nom.)	0.5 s
		Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.57
		Voltage (Nom)	ac electronic 12 V
Light Technical		Temperature	
Colour Code	827 [ CCT of 2,700 K]	T-Case maximum (nom.)	80 °C
Beam Angle (Nom)	300 °		
Luminous flux (nom.)	115 lm	Controls and Dimming	
Colour designation	Warm white (WW)	Dimmable	No
Correlated Colour Temperature (Nom)	2700 K		
Luminous efficacy (rated) (nom.)	115.00 lm/W	Mechanical and Housing	
Colour consistency	<6	Bulb shape	Capsule
Colour rendering index (nom.)	80		
LLMF at end of nominal lifetime (nom.)	70 %		

# CorePro LEDcapsule LV

## Approval and Application


Energy efficiency label (EEL)	A++
Suitable for accent lighting	No
Energy consumption kWh/1,000 hours	1 kWh

## Product Data

Full product code	871869976761700
Order product name	CorePro LEDcapsuleLV 1-10W G4 827

EAN/UPC – product	8718699767617
Order code	76761700
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	929002388802
SAP net weight (piece)	0.008 kg


## Dimensional drawing




Capsule G4 1W-10W 100lm 2700K Non-Dim

Product	D	C
CorePro LEDcapsuleLV 1-10W G4 827	13 mm	35 mm


## Photometric data



LEDcapsule LV 1W G4 827




LEDcapsule LV 1W G4 827



LEDcapsule LV 1W G4

# CorePro LEDcapsule LV

## Lifetime



15K LED

15K LMP

