


Wiha ProStar Holder.

Right Key by Sliding Mechanism.




Practical bolster plate for all small keys.

With ProStar, it is possible to open the holder with only one hand thanks to the new sliding mechanism and the tool thus offers maximum-comfort working.

The optimum user benefit is manifested in the unique mechanism, which can be used to remove each key individually without having to move any of the other keys.

Thanks to the compact design, the ProStar takes up little space on the bench or in the toolbox.



Push red upper part to the right.



Tip the required key forwards...



...and take it out.



Wiha ProStar:

- New sliding mechanism for opening the holder with only one hand
- Quick removal of each individual key without having to move another key
- Compact design saves space on the bench and in the toolbox
- High-quality plastic material, impact-resistant, cadmium free
- New colour-coding system for immediate identification:

 Red upper part: 9 sizes in metric dimensions

 Yellow upper part: 13 sizes in inches

 Green upper part: 13 TORX® keys

Wiha Hex L-Keys with MagicRing®.

Ballpoint Hex L-Keys, Metric.



369R Ballpoint Hex L-Key, Long. With MagicRing®.

Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Standards: Profile, length and hardness according to ISO 2936L.
 Application: Insert screws into or remove from boreholes, especially in areas that are difficult to access.
 Extra: MagicRing® made from spring steel holds all standard screws tight at various angles (available from 3 mm).
 The ballpoint enables the user to work at angles up to 25°.

Order-No.	●	↔	↙	↘	£
20549 2	3	128	23	10	2.50
20550 8	4	142	29	10	2.65
20570 6	5	163	33	10	2.85
20551 5	6	184	38	10	3.35
20552 2	8	206	44	10	4.60
20553 9	10	231	50	5	6.00



369R S9 Ballpoint Hex L-Key Set in ProStar. With MagicRing®, Chrome-plated, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Standards: Profile, length and hardness according to ISO 2936L.
 Application: Insert screws into or remove from boreholes, especially in areas that are difficult to access.
 Extra: Space saving ProStar allows the easy removal of each key without moving any others.
 MagicRing® made from spring steel holds all standard screws tight at various angles (available from 3 mm).
 The ballpoint enables the user to work at angles up to 25°.

Order-No.						↘	£
20709 0	369R S9					5	23.70
●	369	1.5	2	2.5			
●	369R	3	4	5	6	8	10

SB 369R S9 Ballpoint Hex L-Key Set in ProStar. With MagicRing®, Chrome-plated, 9 pcs. Blister Packed.

Order-No.						↘	£
20712 0	SB 369R S9					5	22.30
●	369	1.5	2	2.5			
●	369R	3	4	5	6	8	10

Cardboard Display.



369R SVH1 Display Ballpoint Hex L-Key Sets. With MagicRing®, Chrome-plated, in ProStar, 9 pcs. Carton Display with 10 Pieces.

Order-No.	Content	●	↘	£
23265 8	10 x 369R S9	1.5 - 10	1	236.90

