



# Classic filament LEDbulbs

## CLA LEDBulb DT11.5-100W E27 CRI90A60CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data


General Information		Power (Rated) (Nom)	
Cap base	E27 [ E27]		11.5 W
EU RoHS compliant	Yes	Lamp current (nom.)	65 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	100 W
Switching cycle	20,000X	Starting time (nom.)	0.5 s
Technical type	11.5-100W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.7
		Voltage (Nom)	230 V
Light Technical		Temperature	
Colour Code	927-922 [ CCT of 2,700 K-2,200 K]	T-Case maximum (nom.)	60 °C
Beam Angle (Nom)	270 °		
Luminous flux (nom.)	1521 lm	Controls and Dimming	
Colour designation	Warm Glow (WG)	Dimmable	Yes
Correlated Colour Temperature (Nom)	2700 2200 K		
Luminous efficacy (rated) (nom.)	132.00 lm/W	Mechanical and Housing	
Colour consistency	<6	Lamp Finish	Clear
Colour rendering index (nom.)	90	Bulb shape	A60 [ A 60mm]
LLMF at end of nominal lifetime (nom.)	70 %		
Operating and Electrical		Approval and Application	
Input frequency	50 to 60 Hz	Energy efficiency label (EEL)	A++

# Classic filament LEDbulbs

Energy consumption kWh/1,000 hours	12 kWh
<b>Product Data</b>	
Full product code	871869977096900
Order product name	CLA LEDBulb DT11.5-100W E27 CRI90A60CL
EAN/UPC – product	8718699770969
Order code	77096900

SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002391802
SAP net weight (piece)	0.030 kg


## Dimensional drawing




A60 230V 100W 1521lm 2700–2200K E27 D CL

Product	D	C
CLA LEDBulb DT11.5-100W E27 CRI90A60CL	60 mm	106 mm


## Photometric data



LEDbulb CLA 11,5W A60 E27 927 922 CL



LEDbulb CLA WGD CRI90




© 2021 Philips Lighting B.V. Page 11

LEDbulb CLA 11,5W A60 E27 927 922 CL

# Classic filament LEDbulbs

## Lifetime



15K LED

15K LMP

