

**RoHS  
Compliant**

## Plier Set, Roll Pouch, 5 Piece



26W6263

### Description

Five piece set comes stored in a convenient roll up pouch for easy transport to the job site.

### Includes

- 6" needle nose pliers
- 7" lineman's pliers
- 8" groove pliers
- 6" cutting pliers
- 8" slip joint pliers

## 32 PC Screwdriver Set - Standard Bits



34AH5387

### Description

32-Piece Magnetic Screwdriver Set provides works when and where you need it. The tough magnetic tip hold bits and screws securely in place. The bit block at all the options you need for fastening specialty screws found in electrical boxes, conduit couplers, outlets, and other common job site fixtures.

### Specifications

Dimension	: L: 11.6" (294.6mm) W: 1.25" (31.75mm)
Shank Length	: 3" (76.2mm)
Colour	: Green and Black

### Includes

TORX	: T6, T7, T8, T10, T15, T20, T25
Hex	: 2mm, 3/32", 7/64", 1/8", 9/64", 4mm, 3/16"
Phillips	: #0, #1, #2, #3
Square	: #1, #2, and #3
Clutch bits included	: 5/32" and 3/16" 1/4" Square to 1/4" Hex Adaptor Screwdriver Slotted 3-4, 5-6, 6-8, 8-10, 10-12, 12-14

## 5" Electrical Cutter



38C9186

### Specifications

Function	: Cut up to 18 AWG, 1mm Copper or Aluminium Wire
Material	: Middle Carbon Steel with hardening
Finished	: Black oxide finished
Length	: 5" (127mm)
Weight	: 60g

## Compact Solid / Stranded Wire Stripper / Cutter



**33AH6220**

### Description

Strips and cuts 10 to 20 AWG Solid and Stranded wire. High carbon steel construction with a corrosion resistant black oxide finish, these wire strippers are built for a long life. The built-in spring return is designed to speed up work. The paint filled and pad printed markings allow for easy visibility. Compact size for tight spaces. Lifetime Warranty

### Features

- Strips and cuts wire : 20 / 18 / 16 / 14 / 12 / 10 AWG
- Precision-ground stripping stations for both solid and stranded wire
- Coil spring provides fast self-opening
- Compact size for tight spaces
- Holes in jaw for looping wire
- Pliers nose for working small nuts and pulling wire.
- Shear-type wire cutter at pivot point
- Hardened steel construction for lifetime service
- Dimension: 2.25" × 6.25" D: 0.25" (W×L×D)
- Handle Colour : Green

### Kit Contents

Order Code	Description	Quantity
26W6263	Plier Set, Roll Pouch, 5 Piece	1
34AH5387	32 PC Screwdriver Set - Standard Bits	
38C9186	5" Electrical Cutter	
33AH6220	Compact Solid / Stranded Wire Stripper / Cutter	

### Part Number Table

Description	Part Number
Assortments & Kits	HAND TOOLS PACK

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.