#### Kraftform Kompakt Stubby magazine RA 1, 6 pieces


#### Our Autumn/Winter production innovations











**EAN:** 4013288221124 **Size:** 115x60x40 mm

Part number:05008883001Weight:175 gArticle number:Kraftform Kompakt StubbyCountry of origin:CZ

Customs tariff

Customs tariff 82079030

number:

• Short, compact Stubby shape for working in tight installation spaces, with 6 bits in the integrated magazine

• Ergonomic 2-component Kraftform handle for precise work

Magazin RA 1

• Ratchet function with fine toothing for a low return angle and reversible ring (right, fixed, left)

• Captive and swiveling bit magazine for easy removal and safe storage of bits

• Take it easy tool finder: colour coding according to profile and size

Particularly small bitholding screwdriver with extremely short bit mounting for hard to reach areas. With ratchet function and fine toothing for a low return angle. Easy-to-operate reversible ring (right, fixed, left). Includes 6 tough, universal bits, which are located in a magazine in the handle. The strong permanent magnet in the bit mounting ensures secure holding of the bit. The 2-component Kraftform handle with the practical combination of hard and soft zones allows for a firm grip and precise working. Take it easy tool finder: With size stamping and colour coding by output to help you find the required bit easily.









# Kraftform Kompakt Stubby magazine RA 1, 6 pieces

#### Our Autumn/Winter production innovations



#### Set contents:



#### 851/1 BTZ PH

05056420001 1 x PH 1 x 25 mm 05056422001 1 x PH 2 x 25 mm



#### 867/1 TORX® BTZ



#### 800/1 BTZ

05056064001 1 x 0.8 x 5.5 x 25 mm

### Compact shape



With its compact handle shape and the short blade, the Kraftform Stubbies are particularly suitable for working in confined screwdriving situations.

# Handle with integrated bit magazine



The handle can be opened and thus gives access to the six bits contained in the magazine.

# Swiveling bit magazine



The swiveling bit magazine allows for the bits to be removed easily in almost any situation and cannot be lost. The bits are safely stored.

## Ratchet function



The ratchet mechanism is fine-toothed for a low return angle. The screwdriving directions right/fixed/left can be set with the reversible ring. The magnetic bit mounting is suitable for bits with 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and Wera connection series 1

# Kraftform Kompakt Stubby magazine RA 1, 6 pieces

#### Our Autumn/Winter production innovations


# Wera BE 4 7001 REBEI

#### **BiTorsion Bits**

"Take it easy" tool finder



BiTorsion bits are absolutely premium products. They have a softer BiTorsion zone which reduces the hardness of the shaft by about 20 % in comparison to the drive tip. This means that the peak loads that cause bit breakage and premature wear are absorbed in this zone — something which enhances the service life of the bits.



"Take it easy" tool finder with colour coding according to profiles and size stamp – for simple and rapid accessing of the required