

# Wiha Hex L-Keys.

Inch Sizes.

## Ballpoint Hex L-Keys and Sets.



**369 Zoll** Ballpoint Hex L-Key, Long.  
Inch Sizes.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.  
Standards: Produced acc. To ASME B18.3-1998.  
Application: Especially for inch-sized screws that are difficult to access.  
Extra: The ballpoint enables the user to work at angles up to 25°.

| Order-No. | ● | ↔    | ⊥   | mm | ↔    | £       |
|-----------|---|------|-----|----|------|---------|
| 01422     | 3 | 0.05 | 72  | 13 | 1.27 | 10 0.76 |
| 01423     | 0 | 1/16 | 80  | 15 | 1.59 | 10 0.76 |
| 01431     | 5 | 5/64 | 88  | 18 | 1.98 | 10 0.76 |
| 01427     | 8 | 3/32 | 101 | 20 | 2.38 | 10 0.77 |
| 01433     | 9 | 7/64 | 111 | 21 | 2.78 | 10 0.82 |
| 01425     | 4 | 1/8  | 121 | 23 | 3.18 | 10 0.86 |
| 01434     | 6 | 9/64 | 136 | 27 | 3.57 | 10 0.95 |
| 01430     | 8 | 5/32 | 148 | 29 | 3.97 | 10 1.16 |
| 01426     | 1 | 3/16 | 163 | 33 | 4.76 | 10 1.38 |
| 01432     | 2 | 7/32 | 176 | 36 | 5.56 | 10 1.50 |
| 01424     | 7 | 1/4  | 191 | 38 | 6.35 | 10 1.76 |
| 01429     | 2 | 5/16 | 210 | 43 | 7.94 | 10 2.60 |
| 01428     | 5 | 3/8  | 232 | 50 | 9.53 | 5 3.45  |



**369 SZ13B** Ballpoint Hex L-Key Set in ProStar.  
Manganese-phosphated, 13 pcs. Inch Sizes.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.  
Standards: Produced acc. To ASME B18.3-1998.  
Application: Especially for inch-sized screws that are difficult to access.  
Extra: Space saving ProStar allows the easy removal of each key without moving any others.

| Order-No. | ↔  | £       |
|-----------|--|---------|
| 24189     | 6 369 SZ13B  | 5 20.20 |
| ●         | 369 Zoll 0.05 1/16 5/64 3/32 7/64 1/8 9/64 5/32 3/16 7/32 1/4 5/16 3/8 |         |

**SB 369 SZ13B** Ballpoint Hex L-Key Set in ProStar.  
Manganese-phosphated, 13 pcs. Inch Sizes.  
Blister Packed.

| Order-No. | ↔  | £       |
|-----------|--|---------|
| 24851     | 2 SB 369 SZ13B   | 5 19.20 |
| ●         | 369 Zoll 0.05 1/16 5/64 3/32 7/64 1/8 9/64 5/32 3/16 7/32 1/4 5/16 3/8 |         |

## Ballpoint Hex L-Key Sets.



**369 HZ8** Ballpoint Hex L-Key Set in Holder.  
Manganese-phosphated, 8 pcs. Inch Sizes.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.  
Standards: Produced acc. To ASME B18.3-1998.  
Application: Especially for inch-sized screws that are difficult to access.  
Extra: Popular key sizes kept in a well-organized holder.

| Order-No. | ↔  | £       |
|-----------|--|---------|
| 01420     | 9 369 HZ8                                      | 5 16.30 |
| ●         | 369 Zoll 5/64 3/32 1/8 5/32 3/16 7/32 1/4 5/16 |         |

**SB 369 HZ8** Ballpoint Hex L-Key Set in Holder.  
Manganese-phosphated, 8 pcs. Inch Sizes.  
Blister Packed.

| Order-No. | ↔  | £       |
|-----------|--|---------|
| 02939     | 5 SB 369 HZ8                                   | 5 15.70 |
| ●         | 369 Zoll 5/64 3/32 1/8 5/32 3/16 7/32 1/4 5/16 |         |



**369 BZ8** Ballpoint Hex L-Key Set in Sliding Box.  
Manganese-phosphated, 8 pcs. Inch Sizes.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.  
Standards: Produced acc. To ASME B18.3-1998.  
Application: Especially for inch-sized screws that are difficult to access.  
Extra: The ballpoint enables the user to work at angles up to 25°. Large, impact resistant sliding box.

| Order-No. | ↔  | £       |
|-----------|--|---------|
| 01412     | 4 369 BZ8                                      | 5 21.60 |
| ●         | 369 Zoll 5/64 3/32 1/8 5/32 3/16 7/32 1/4 5/16 |         |