

Wiha ComfortGrip.

Soft Zones for Maximum Working Comfort.



Side blade with through blade.

The new Wiha T-handle with through blade for additional side blade features soft zones for the comfortable transmission of high torques.

Due to their ergonomic design, these handles are comfortable to hold. Fewer pressure points and less strain on the user mean that these tools are a pleasure to use.

When using the side blade, a supporting hand on the handle produces additional stability, which prevents the blade from suddenly slipping out of the screw head. This is better for both blade and screw.

The hole in the handle can be used for shop storage.



No screw can resist. The powerful Wiha ComfortGrip is quick and comfortable to use and even loosens screws that have been glued into position.



A tool that is a pleasure to use. Using the side blade for even greater torque, a supporting hand stabilises the handle and prevents the blade from slipping.



Black soft zones in the handle for comfortable working.



Chrome-plated blade for optimum corrosion protection.



Wiha ComfortGrip:

- The integrated side blade is particularly useful when loosening or tightening screws that are rusted-in, glued into position or particularly hard to move
- The through blade withstands even the highest stresses
- Distinctive soft zones on the ergonomic handle for the comfortable transmission of even high torques
- Handle-size concept with three handle shapes designed for maximum ease of use and for applying just the right amount of torque
- The new colour-coding system for the handles couldn't be clearer:
 - Red: metric hex blades
 - Green: TORX® profiles
- Matt chrome-plated blades guarantee optimum corrosion protection and a long service life for the whole blade

Wiha ComfortGrip T-Handle.

Soft Zones for Maximum Working Comfort.

Hex Driver.



334DSR Hex Driver with ComfortGrip. With MagicRing® and Side Blade.

- Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Wiha ComfortGrip, the comfortable multi-component T-handle with soft zones for maximum working comfort.
 Application: For comfortable high torque transfer and to insert and remove screws from holes. Especially useful for loosening or tightening screws that are hard to move.
 Extra: MagicRing® made from spring steel holds all standard screws tight at various angles (available from 3 mm).
 One piece blade, through the handle withstands even the highest stresses.

Order-No.	●	≡	☞	⊥	⊥	≡	£
26135 1	3	100	13	80	26	10	4.05
26136 8	4	150	13	80	26	10	4.75
26137 5	5	150	17	100	32	10	4.95
26138 2	6	150	17	100	32	10	5.50
26139 9	8	200	17	100	32	10	7.00
26140 5	10	200	22	120	38	10	10.80



334DS Hex Driver with ComfortGrip. With Side Blade.

- Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Wiha ComfortGrip, the comfortable multi-component T-handle with soft zones for maximum working comfort.
 Application: For comfortable high torque transfer. Especially useful for loosening or tightening screws that are hard to move.
 Extra: One piece blade, through the handle withstands even the highest stresses.

Order-No.	●	≡	☞	⊥	⊥	≡	£
26164 1	2	100	13	80	26	10	2.85
26165 8	2.5	100	13	80	26	10	2.90
26166 5	3	100	13	80	26	10	2.75
26167 2	4	150	13	80	26	10	3.00
26168 9	5	150	17	100	32	10	3.45
26169 6	6	150	17	100	32	10	3.65
26170 2	8	200	17	100	32	10	4.80
26171 9	10	200	22	120	38	10	8.10

TORX® Driver and Sets.



364DS TORX® Driver with ComfortGrip. With Side Blade.

- Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Wiha ComfortGrip, the comfortable multi-component T-handle with soft zones for maximum working comfort.
 Application: For comfortable high torque transfer. Especially useful for loosening or tightening screws that are hard to move.
 Extra: One piece blade, through the handle withstands even the highest stresses.
 ChromTop® blade tip for the highest accuracy at both ends

Order-No.	⊕	≡	☞	⊥	⊥	≡	£
26172 6	T10	100	13	80	26	10	6.00
26173 3	T15	100	13	80	26	10	6.30
26174 0	T20	100	17	100	32	10	6.80
26175 7	T25	150	17	100	32	10	6.80
26176 4	T27	150	17	100	32	10	7.00
26177 1	T30	150	17	100	32	10	7.10
26178 8	T40	150	17	100	32	10	7.40



334DS K6 Hex Driver Set with ComfortGrip. Blister Packed, 6 pcs.

Order-No.	●	≡	£
26247 1	334DS K6	1	19.80
●	334DS	2.5 3 4 5 6 8	



364DS K6 TORX® Driver Set with ComfortGrip. Blister Packed, 6 pcs.

Order-No.	⊕	≡	£
26248 8	364DS K6	1	38.30
⊕	364DS	T10 T15 T20 T25 T30 T40	