



Einhell

CLASSIC

High Pressure Cleaner

TC-HP 90

Item No.: 4140740

Ident No.: 11019

Bar Code: 4006825649857

The Einhell TC-HP 90 high-pressure cleaner provides an impressive combination of compact design with a power rating of 1,200 W. Thanks to the compact design and integrated central carry-handle it is easy to work with and saves space when stowed away. Being low in weight the cleaner is ideal for mobile use and suitable for getting lightly soiled surfaces cleaned quickly with a max. flow rate of 372 liters/h. The water connection has an integral filter. For flexibility in use it has a modular Quick-Couple-system. There are also versatile storage options for accessories. The product is supplied complete with a gun, 3m pressure hose, lance and point/wide nozzle.

Features & Benefits

- Small and compact design
- Space-saving storage
- Integrated central carry-handle for user-friendly transportation
- Gets lightly soiled surfaces cleaned quickly with 372 l/h
- Water connection with integral filter
- Ideally suited for mobile use thanks to low weight
- Modular Quick-Couple system for versatile usage of accessories
- Versatile storage options for nozzles, gun, etc.
- Including: gun, 3m pressure hose, lance and point/wide nozzle




Technical Data

- Mains supply	207-234 V 50/60 Hz
- Power	1200 W
- Pressure max.	90 bar
- Flow rate max.	372 L/h
- Max. water temperature	40 °C
- Max. inlet water pressure	7 bar
- Length of high-pressure hose	3 m



Logistic Data

- Product weight	3.9 kg
- Gross weight single packaging	4.8 kg
- Dimensions single packaging	240 x 200 x 374 mm
- Pieces per export carton	1 Pieces
- Gross weight export carton	4.8 kg
- Dimensions export carton	245 x 200 x 368 mm
- Container quantity (20"/40"/40"HC)	1518 3036 3542



Available as special accessories



Patio Cleaner
High Pressure Cleaner Accessor
Item No.: 4144015
Bar Code: 4006825652000
Einhell Accessory



Horizontal brush
High Pressure Cleaner Accessor
Item No.: 4144018
Bar Code: 4006825652260
Einhell Accessory



PVC High Pressure hose 6m
High Pressure Cleaner Accessor
Item No.: 4144019
Bar Code: 4006825652277
Einhell Accessory



turbo nozzle
High Pressure Cleaner Accessor
Item No.: 4144022
Bar Code: 4006825652307
Einhell Accessory



metal extension
High Pressure Cleaner Accessor
Item No.: 4144024
Bar Code: 4006825652321
Einhell Accessory



Fix Brush
High Pressure Cleaner Accessor
Item No.: 4144016
Bar Code: 4006825652246
Einhell Accessory



Angled Nozzle
High Pressure Cleaner Accessor
Item No.: 4144020
Bar Code: 4006825652284
Einhell Accessory



Foam producer
High Pressure Cleaner Accessor
Item No.: 4144021
Bar Code: 4006825652291
Einhell Accessory



pipe cleaning hose 15 m
High Pressure Cleaner Accessor
Item No.: 4144023
Bar Code: 4006825652314
Einhell Accessory