

# GT730-4H-SL-2GD5

**Auto-Extreme technology for better Performance & Longevity!**


## ASUS Exclusive Innovations

- The **ASUS GeForce® GT 730 Graphics Card** features 4x HDMI ports and passive cooling in a single slot, enabling quiet multi-monitor productivity.



### ■ Auto-Extreme Technology

An automated manufacturing process that enhances reliability.



### ■ 4x HDMI Ports

Enable multi-monitor productivity with support for up to 4 external displays connected to the built-in HDMI ports.



## ■ GPU Tweak II

This powerful software provides intuitive performance tweaking, thermal controls, and system monitoring



## ■ Passive Cooling

A passively-cooled design creates a quieter workspace.




## ■ Single-slot Design

A compact design increases compatibility with other PCIe peripherals and even allows multiple ASUS GT730s to be stacked in a single system.



## I/O Specifications



## ASUS Features

**GDDR5**  
**2GB**  
Memory

- **Gigantic 2GB GDDR5 Memory:**  
On-board memory for the best gaming experience & the best resolution

## GPU Features



- **GEFORCE GT 730(64-bit)**



- **NVIDIA® Adaptive V-Sync :**  
NVIDIA Adaptive Vertical Sync adjusts VSync to current frame rates for maximum playability



- **NVIDIA® PhysX® ready:**  
Dynamic visual effects like blazing explosions, reactive debris, realistic water, and lifelike characters



- **Microsoft DirectX 12**  
Brings new levels of visual realism to gaming on the PC and get top-notch performance.



- **Microsoft® Windows 10 compatible**  
Gives you access to advanced computing experiences with the latest operating system so you get more done with your PC

## Hardware Specification

Model	GT730-4H-SL-2GD5
Graphics Engine	NVIDIA GeForce® GT 730
CUDA Cores	384
Bus Standard	PCI-E 2.0
OpenGL	OpenGL® 4.6
GPU Clock	OC mode : 927 MHz (Boost Clock) Gaming mode : 902 MHz (Boost Clock)
Video Memory	2GB GDDR5
Memory Clock	5010 MHz
Memory Interface	64 bit
I/O	4 x Native HDMI 1.4b
HDCP Compliant	HDCP 2.2
Digital Max. Resolution	3840 x 2160
Maximum Display Support	4
NVLink/ Crossfire Support	NA
Recommended PSU	300 W
Package Contents	1 x Speedsetup Manual
Software Bundled	ASUS GPU Tweak II & Driver (please download all software from the support site)
Slot	1 slot
Dimension	
Card Size (cm/inch)	14.8 x 10.5 x 1.8cm 5.8 x 4.1 x 0.7 inches
Color Box (mm)	228 x 163 x 50 mm
Weight	
Single Card (KG)	0.211
Product Weight (with packing) (KG)	0.417
Note	<p>* Our wattage recommendation is based on a fully overclocked GPU and CPU system configuration. For a more tailored suggestion, please use the "Choose By Wattage" feature on our PSU product page: <a href="https://rog.asus.com/event/PSU/ASUS-Power-Supply-Units/index.html">https://rog.asus.com/event/PSU/ASUS-Power-Supply-Units/index.html</a> * All specifications are subject to change without notice. Please check with your supplier for exact offers. Products may not be available in all markets. If you do not use the latest and current specifications of ASUS products, you shall be liable for all loss and damage claimed by third party to ASUS based on false advertising or any other issues caused from using false specifications of ASUS products.</p>

