

Weller®

WLIBA4 Cordless Battery Powered Soldering Tool

Thank you for purchasing the WLIBA4 battery powered cordless soldering tool from Weller®. This is the latest in a line of both cordless and corded soldering and hot air tools from Weller – the world's leading maker of soldering products. With proper care, your WLIBA4 tool will give you years of reliable service.


WLIBA4 is a lightweight, fast heat-up soldering iron ideal for field service work where electricity is not readily available. The heating element coil is contained in the tip for super-fast heat-up. Use this tool for light duty soldering jobs where portability is necessary.

Safety Notes


1. Tip is HOT! Do not touch the tip or you may get severely burned.
2. Do not immerse in water!
3. Allow the tip to cool after use before storing away.
4. Place the protective cover over the tip when storing so that the cover secures the safety slide switch in the "Off" position.
5. **Warning:** This product contains, or when used for soldering and similar applications produces chemicals known to the State of California to cause cancer and birth defects (or other reproductive harm).

Operating Instructions

1. To install batteries, remove the battery cover by pinching the clips on the sides of the battery cover and lifting off.
2. Place (3) 1.5V size AA alkaline batteries (included) into the iron as illustrated and replace the cover.



3. Remove the protective cover from the tip.
4. Make sure the tip is securely installed.
5. Slide the On/Off switch to the "On" position.
6. Hold the soldering iron like a pen. The iron heats up to solder melting point in about 30 seconds.
7. To extend battery life, only press the button when soldering.
8. Place the hot soldering iron standing upright so the tip does not come in contact with surrounding objects.
9. After soldering, slide the switch to the "OFF" position and replace the protective cover



Maintenance

1. If it takes more than 60 seconds to reach working temperature, install fresh batteries.
2. Use alkaline batteries for best results. Do not mix old and new batteries.

3. Do not change the soldering tip when hot. Use the tip exchanger provided to remove the tip as shown.
4. The soldering tip is iron plated for long life. Do not file the tip as filing will destroy the plating.
5. Remove the batteries from the tool when not using for prolonged periods to prevent batteries from leaking into the tool.

Spare Tips

Cat. No.	Description
WLTC03IBA4	Conical

Weller® Consumer Soldering Iron Warranty

Apex Tool Group, LLC warrants this product will be free from defects in material and workmanship for a period of seven (7) years from the date of purchase. No warranty is made with respect to products which have been (a) altered, modified or repaired by anyone other than Apex Tool Group, LLC; (b) subject to abuse, improper use, negligence, accident or improper storage; (c) installed, used or maintained not in accordance with normal practices or the instructions and specifications of Apex Tool Group, LLC; or (d) used in conjunction with any product, device, component or system, that is either defective, the source of a defect, or not reasonably intended to be used in conjunction with this product.

The foregoing limited warranty is exclusive and in lieu of all other warranties, whether expressed, implied or statutory, including, but not limited to, any warranty of merchantability or fitness for any particular purpose. The obligation of Apex Tool Group, LLC under this limited warranty is expressly limited to repairing the product, refunding the purchase price or replacing the product, at the sole and absolute discretion of Apex Tool Group, LLC, at no charge to Buyer.

The remedies provided for herein shall constitute the sole recourse of Buyer against Apex Tool Group, LLC whether the claim is made in tort or in contract, including claims based on warranty, negligence, strict liability, deceit, fraud, misrepresentation or otherwise. In no event shall Apex Tool Group, LLC be liable for special, indirect, incidental or consequential damages (regardless of the form of action), nor for lost profits. Apex Tool Group, LLC liability for any claims or damages arising out of or connected with the manufacture, sale, delivery, use, maintenance, repair or modification of this product shall not exceed its purchase price.

Apex Tool Group, LLC will, during the warranty period, repair, replace or refund the purchase price of any product found to be defective in accordance with this limited warranty. Return freight prepaid with proof of purchase to: For USA; Apex Tool Group, LLC 1000 Lufkin Road, Apex, NC 27539.