

PERFORMANCE

Processor

Intel® Core™ i5-10500 (6C / 12T, 3.1 / 4.5GHz, 12MB)

Graphics

Integrated Intel UHD Graphics 630

Chipset

Intel H470 Chipset

Memory

1x 8GB UDIMM DDR4-2666

Memory Slots

Four DDR4 DIMM slots, dual-channel capable

Max Memory

Up to 128GB DDR4-2933

Storage

1x 256GB SSD M.2 2280 PCIe x4 NVMe Opal

Storage Support

Up to three drives, 1x 2.5"/3.5" HDD + 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB each
- 3.5" HDD up to 2TB
- M.2 SSD up to 2TB
- Optional Intel Optane™ Memory, M.2

Card Reader

3-in-1 Card Reader

Optical

DVD±RW

Audio Chip

High Definition (HD) Audio, Realtek® ALC623-CG codec

Speakers

1Wx1

Power Supply

180W 85%

DESIGN

Keyboard

USB Traditional Keyboard, Black, English (UK)

Mouse

USB Calliope Mouse, Black

Expansion Slots

- Two dummy slots, only brackets for optional port extension
- One PCIe 3.0 x1, low-profile (length < 155mm, height < 68mm)
- One PCIe 3.0 x16, low-profile (length < 155mm, height < 68mm)
- Two M.2 slots (one for WLAN, one for SSD)

Case Color

Black

Form Factor

SFF (8.2L)

Dimensions (WxDxH)

93 x 298 x 340 mm (3.6 x 11.7 x 13.4 inches)

Weight

5.3 kg (11.7 lbs)

CONNECTIVITY

Ethernet

Integrated 100/1000M

Front Ports

- 1x USB-C 3.2 Gen 1
- 1x microphone (3.5mm)
- 2x USB 3.2 Gen 2
- 2x USB 3.2 Gen 1
- 1x headphone / microphone combo jack (3.5mm)

Optional Front Ports (configured)

1x card reader

Rear Ports

- 2x DisplayPort™
- 1x Ethernet (RJ-45)
- 1x serial (9-pin)
- 4x USB 2.0
- 1x line-out (3.5mm)
- 1x HDMI®

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified

Fingerprint Reader

No fingerprint reader

Physical Locks

- Kensington® Security Slot
- Padlock Loop

Chassis Intrusion Switch

Chassis Intrusion Switch

SERVICE

Base Warranty

3-year, Onsite

CERTIFICATIONS

Green Certifications

- TCO Certified 8.0
- RoHS compliant
- ErP Lot 3

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation)

SOFTWARE

Operating System

Windows® 10 Pro 64, English

MODEL

TopSeller : Yes

Announce Date : 2020-05-19

EAN / UPC / JAN : 0194778491976

End of Support : 2026-12-19



Premier Support - A direct 24x7x365 line to our most elite technicians.

Advanced technical support, 24x7x365, in more than 100 markets

Technical Account Managers for proactive relationship and escalation management

Comprehensive hardware & OEM software support

Priority on service delivery and repair parts

Single point of contact for simplified end-to-end case management

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security – the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

ThinkPad UltraSlim USB DVD Burner

4XA0E9775

ThinkPad UltraSlim USB DVD Burner -- is a small form factor external portable DVD and CD recordable drive that can be attached to Notebooks with USB2.0 port or USB3.0 port. With 9.5mm UltraSlim engine, 20% slimmer tha...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

PSREF

Product Specifications
Reference