



CorePro LEDspot MV

CoreProLEDspot 4-50W GU10 827 36D DIM UK

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap base	GU10 [GU10]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	50,000X
Light Technical	
Colour Code	827 [CCT of 2,700 K]
Beam Angle (Nom)	36 °
Luminous flux (nom.)	345 lm
Luminous intensity (nom.)	700 cd
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	86.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	345 lm
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W
Lamp current (nom.)	23 mA


Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.84
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	70 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	PAR16 [PAR 2 inch]
Approval and Application	
Energy Efficiency Class	F
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	4 kWh
	400299
Product Data	
Full product code	871869672137701

CorePro LEDspot MV

Order product name	CoreProLEDspot 4-50W GU10 827 36D DIM UK
EAN/UPC – product	8718696721377
Order code	72137701
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10

SAP material	929002495999
SAP net weight (piece)	0.048 kg


Dimensional drawing




GU10 220-240V 4-50W 345lm 36D 2700K D

Product	D	C
CoreProLEDspot 4-50W GU10 827 36D DIM UK	50 mm	54 mm


Photometric data



LEDspots Corepro SLR 4W PAR16 GU10 827 36D-LDD



LEDspots Corepro SLR 4W PAR16 GU10 827 36D-POC



Copyright Clearance Center, Inc.	Not for Redistribution	Page 13
----------------------------------	------------------------	---------

LEDspots Corepro SLR 4W PAR16 GU10 827 36D-ADL

CorePro LEDspot MV

Lifetime



15K LED



15K LMP

