



# CorePro Glass LED bulbs

## CorePro LEDBulbND 7-60W E27 WW A60 CL G

Featuring a classic heritage design, Classic filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. A very easy choice for people who are looking to replace retrofit LED bulbs: compared to conventional lamps, it provides a 90% energy-saving. The CorePro Glass LED bulbs provides excellent quality of light. By offering a lifetime of 15,000 hours, it reduces maintenance costs.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
	Sphere

Light Technical	
Colour Code	827 [ CCT of 2,700 K]
Luminous flux (nom.)	806 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	115.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz

Power (Rated) (Nom)	7 W
Lamp current (nom.)	60 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.51
Voltage (Nom)	220-240 V

Temperature	
T-Case maximum (nom.)	45 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	A60 [ A 60mm]

# CorePro Glass LED bulbs

## Approval and Application

Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	7 kWh
	387390

## Product Data

Full product code	871951438003500
Order product name	CorePro LEDBulbND 7-60W E27 WW A60 CL G

EAN/UPC – product	8719514380035
Order code	38003500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929001387362
SAP net weight (piece)	0.030 kg



## Dimensional drawing



Product	D	C
CorePro LEDBulbND 7-60W E27 WW A60 CL G	60 mm	104 mm


## Bulb A60 230V 7-60W 806lm 2700K E27 ND

## Photometric data



## LEDbulb 60W E27 827 CL A60 ND


## LEDbulb 60W E27 827 CL A60 ND




## LEDbulb 60W E27 827 CL A60 ND

# CorePro Glass LED bulbs

## Lifetime



LEDbulb 60W E27 827 CL A60 ND



LEDbulb 60W E27 827 CL A60 ND

