# Cable Assembly HDMI to DisplayPort Plug with Latch





## RoHS Compliant

#### **Features**

- · Compliant with DP1.2 specification.
- · Connect a DisplayPort (DP, DP++, DisplayPort++) equipped computer to a HD monitor or projector with HDMI connector.
- Support HBR bandwidth and resolutions up to 4K × 2K@30Hz.
- · Gold-plated connector provides superior transmission, high reliability and durability.
- Deliver high definition audio and video signals from your computer to a monitor for video streaming or gaming.
- DisplayPort connector with latches keeps cable securely plugged in.
- · Support DisplayPort1.2 and 4 lanes.
- Support DisplayPort 1.2a input and HDMI1.4b output.
- Support HDMI highest video resolution 4K × 2K@30Hz.
- Support multiple color formats: RGB 6/8/10/12-bit per component (bpc) and YCbCr4:4:4, YCbCr4:2:2, 8/10/12bpc.
- HDMI 1.4a compliant with maximum data rate 3.0Gbps.
- Support 10/12-bit deep color 1080p up to 2.25Gbps and 3D video formats (720p@50/59.94/60Hz, 1080i@50/59.94/60Hz, 1080p@23.98/24Hz, 1080p@50/59.94/60Hz) up to 2.97Gbps.
- Content protection of HDCP Rx and Tx keys to support HDCP repeater.
- · Support up to 8 channel LPCM, compressed audio (AC-3,DTS) and HBR audio format.
- Support up to 192 khz audio frame rate and up to 24-bit audio sample size.
- Integrated both HDCP Rx and Tx keys to support HDCP repeater.
- Powered from DisplayPort source.

### Specification

Connector Type A : DisplayPort Plug
Connector Type B : HDMI Plug

Cable Length - Imperial : 6ft
Cable Length - Metric : 1.83m
Jacket Color : Black

#### Part Number Table

Description	Part Number
Cable Assembly, DisplayPort Plug to HDMI Plug, 6 ft, Black	10DP-DPHM2-06

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. MCM is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

