



# Einhell

# EXPERT

## POWER X-CHANGE

**Cordless Hot Glue Gun**

**TE-CG 18 Li - Solo**

**Item No.: 4522200**

Ident No.: 11018

Bar Code: 4006825641202

The Einhell TE-CG 18 Li - Solo cordless hot glue gun is a member of the Power X-Change series from Einhell and is powered by a long-lasting lithium-ion rechargeable battery. All the rechargeable batteries from the system series can be combined with the glue gun. This handy glue gun is ready to use after only a 120-second warm-up. The practical LED display shows the heat status at-a-glance and the glue gun switches off automatically after 5 minutes without being used. The additional flat glue nozzle is ideal for jobs with specific requirements. For safe and comfortable handling it has a softgrip. Five glue sticks are included. This product comes without a battery and charger which are available separately, e.g. as a PXC starter set.

## Features & Benefits

- A member of the Power X-Change family
- Practical LED heat level indicator
- Operational for glueing after only 120 seconds of warm-up time
- Safe and comfortable handling thanks to the soft grip
- Auto. switch-off after 5 min. standby to prevent from overheating
- Practical LED for optimum illumination of the working area
- Additional flat glueing nozzle optimum usage in narrow spaces
- Incl. 5 glue sticks, with a length of 200 mm
- Supplied without battery and charger (available separately)

## Technical Data

- Heat-up time 120 s
- Max. glueing temperature 170 °C
- Glue stick diameter 11 mm

## Logistic Data

- Product weight (kg) 0.29
- Gross weight (kg) 0.76
- Pieces per export carton 5 Pieces
- Gross weight of export carton 4.05 kg
- Dimensions export carton 340 x 240 x 215 mm
- Container quantity (20"/40"/40"HC) 7835 | 16385 | 19235



LED HEATING INDICATOR



LED



CHANGE ABLE NOZZLE



INCL.



Testergebnis  
**sehr gut (1,0)**  
Oberklasse



**18 V**



**2 min.**

**FAST START**



**DRIP CONTROL**

## Available as special accessories



Power X-Boostcharger 6A  
Charger  
Item No.: 4512064  
Bar Code: 4006825629019  
Einhell Accessory



18V 2,0Ah Power X-Change  
Battery  
Item No.: 4511395  
Bar Code: 4006825610369  
Einhell Accessory



18V 4,0Ah Power X-Change 1  
Battery  
Item No.: 4511396  
Bar Code: 4006825610376  
Einhell Accessory



18V 5,2Ah Power X-Change Plus  
Battery  
Item No.: 4511437  
Bar Code: 4006825616606  
Einhell Accessory



Power X-Twincharger 3A  
Charger  
Item No.: 4512069  
Bar Code: 4006825629729  
Einhell Accessory



18V 3,0 Ah Power-X-Change  
Battery  
Item No.: 4511341  
Bar Code: 4006825590593  
Einhell Accessory

18V 4,0Ah PXC Starter Kit 2  
PXC-Starter-Kit  
Item No.: 4512042  
Bar Code: 4006825613704  
Einhell Accessory



18V 2,0Ah PXC Starter Kit  
PXC-Starter-Kit  
Item No.: 4512040  
Bar Code: 4006825613681  
Einhell Accessory

## Battery-Running-Times

One Battery for All	gluing <sup>1</sup> (pieces)
1.5 Ah	14
2.0 Ah	18
2.5 Ah	22
3.0 Ah	28
4.0 Ah	36
5.2 Ah	44
6.0 Ah	50

### Test setup:

1) glue sticks