



# CorePro Glass LED bulbs

## CorePro LEDBulbND 8.5-75W E27 A60 827CLG

Featuring a classic heritage design, Classic filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. A very easy choice for people who are looking to replace retrofit LED bulbs: compared to conventional lamps, it provides a 90% energy-saving. The CorePro Glass LED bulbs provides excellent quality of light. By offering a lifetime of 15,000 hours, it reduces maintenance costs.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
	Sphere
Light Technical	
Colour Code	827 [ CCT of 2,700 K]
Luminous flux (nom.)	1055 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	124.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz


Power (Rated) (Nom)	8.5 W
Lamp current (nom.)	70 mA
Wattage equivalent	75 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.52
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	A60 [ A 60mm]

CorePro Glass LED bulbs

Approval and Application	
Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	9 kWh
	387423
Product Data	
Full product code	871951434712000
Order product name	CorePro LEDBulbND 8.5-75W E27 A60 827CLG

EAN/UPC – product	8719514347120
Order code	34712000
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002025492
SAP net weight (piece)	0.030 kg


Dimensional drawing




Bulb A60 75W 1055lm 2700K E27 ND Clear

Product	D	C
CorePro LEDBulbND 8.5-75W E27 A60 827CLG	60 mm	104 mm


Photometric data



LED Bulb A67 E27 ND Clear




LED Bulb A67 E27 ND Clear




LED Bulb A67 E27 ND Clear

CorePro Glass LED bulbs

Lifetime



LED Bulb A67 E27 ND Clear



LED Bulb A67 E27 ND Clear

