

# Corepro Glass High Lumen bulbs

## CorePro LEDBulbND17-150W E27 A67 827 CLG

Featuring a classic heritage design, Classic filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. A very easy choice for people who are looking to replace retrofit LED bulbs: compared to conventional lamps, it provides a 90% energy-saving. The CorePro Glass LED bulbs provides excellent quality of light. By offering a lifetime of 15,000 hours, it reduces maintenance costs.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
	Sphere
Light Technical	
Colour Code	827 [ CCT of 2,700 K]
Luminous flux (nom.)	2452 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	144.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz

Power (Rated) (Nom)	17 W
Lamp current (nom.)	140 mA
Wattage equivalent	150 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.51
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	A67 [ A 67mm]

# Corepro Glass High Lumen bulbs

## Approval and Application


Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	17 kWh 374867

## Product Data

Full product code	871951434744100
Order product name	CorePro LEDBulbND17-150W E27 A67 827 CLG

EAN/UPC – product	8719514347441
Order code	34744100
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002055092
SAP net weight (piece)	0.040 kg


## Dimensional drawing




Bulb 14-150W 2452lm 2700K E27 ND Clear

Product	D	C
CorePro LEDBulbND17-150W E27 A67 827 CLG	70 mm	128 mm


## Photometric data



LEDbulb E27 A67 827 CL





LEDbulb 17-150W E27 A67



LEDbulb 6,5-60W E14 B35

# Corepro Glass High Lumen bulbs

## Lifetime



LEDbulb 6,5-60W E14 B35

LEDbulb 6,5-60W E14 B35

