



CorePro GLASS LED candles and lusters

CorePro LEDCandle ND6.5-60W B35E14827CLG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lusters, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED candles and lusters provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information	
Cap-Base	E14 [E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Flux measurement reference	Sphere
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	124.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Nom)	6.5 W
Lamp Current (Nom)	50 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.55
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35 [B 35mm]

CorePro GLASS LED candles and lusters

Approval and Application


Energy Efficiency Class	E
Energy Consumption kWh/1000 h	7 kWh
EPREL Registration Number	387441

Product Data

Full product code	871951434746500
Order product name	CorePro LEDCandle ND6.5-60W B35E14827CLG

EAN/UPC - Product	8719514347465
Order code	929002028092
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929002028092
Net Weight (Piece)	0.012 kg


Dimensional drawing




Candle B35 60W 806lm 2700K E14 ND Clear

Product	D	C
CorePro LEDCandle ND6.5-60W B35E14827CLG	35 mm	97 mm

Photometric data




LEDbulb 6,5-60W E14 B35



LEDbulb 6,5-60W E14 B35

CorePro GLASS LED candles and lusters



Photometric data



© Philips Lighting N.V. 2021

LEDcandle E14 B35 827 CL

Lifetime



LEDbulb 6,5-60W E14 B35

LEDbulb 6,5-60W E14 B35

