

DYMO®

LabelWriter™ 5XL

NEW
&
IMPROVED



ONLY WORKS WITH
AUTHENTIC
DYMO
LABELS

Ink-Free PC/Mac® XL Shipping Label Printer with LAN Connection

- Direct thermal print technology eliminates the need for ink or toner
- Create and customize 60+ label types through USB or connect to a network through LAN connection with free DYMO® Connect™ for desktop software
- Print 104 mm x 159 mm shipping labels directly from Amazon™, eBay™, Etsy™, Poshmark® and more
- Print from UPS®, FedEx®, USPS® and more through third party software integration
- Print crystal clear barcodes, text, graphics and more with 300 dpi resolution



Automatic Label Recognition

New Automatic Label Recognition recognizes the label size and type, ensuring no more misprints. Never run out of labels without notice.



Labels In. Guesswork Out.



104 mm x 159 mm
Shipping Labels



Inventory Management



General Organization



Pack Contents:

- LabelWriter 5XL Label Printer
- 1 XL Shipping Label Starter Roll (104 mm x 159 mm)
- Power Adapter
- Power Cable
- USB Cable
- Quick Start Guide
- 2 + 1 Year Limited Warranty**

Machine Specifications

SKU Description	DY LW 5XL PRINTER UK/HK
SKU Number	2112724
EAN	3026981127243
Unit Dimensions	25 cm x 25 cm x 26 cm
Weight	2.1 kg
Compatibility	PC and Mac® via DYMO® Connect™ for Desktop Software
Connectivity	USB and LAN
Max Label Width	104 mm
Print Resolution	300 dpi
Printing Technology	Direct Thermal
Print Speed	53 labels/minute*
Barcode Printing	Yes
Power Source	Power Adapter
Country of Origin	China

* 4 line address label via USB connection

** +1 year if registered on the DYMO® website

DYMO®

LabelWriter™ 5XL

ONLY WORKS WITH
AUTHENTIC
DYMO®
LABELS



Labels made
in Belgium



FSC® certified
paper labels



BPA free
paper labels



No ink
or toner



Recycled
packaging

LabelWriter™ Standard Labels

Style	Description	Item #	Size (mm)	Labels x Roll/Box	Adhesive	Material
Address 	Standard Address Labels	S0722370	28 x 89	130 x 2	Permanent	Paper
	Standard Address Labels	S0722360	28 x 89	130 x 24	Permanent	Paper
	Standard Address Labels	2093091	28 x 89	130 x 12	Permanent	Paper
	Assorted Colour Labels	S0722380	28 x 89	130 x 4	Permanent	Paper
	Standard Address Labels	1983173	28 x 89	130 x 1	Permanent	Paper
	Large Address Labels	1983172	36 x 89	260 x 1	Permanent	Paper
	Large Address Labels	2093093	36 x 89	240 x 12	Permanent	Paper
	Large Address Labels	S0722400	36 x 89	260 x 2	Permanent	Paper
	Large Address Labels	S0722390	36 x 89	260 x 24	Permanent	Paper
	Large Address Labels	S0722410	36 x 89	260 x 1	Permanent	Transparent Plastic
	Large Return Address Labels	S0722520	25 x 54	500 x 1	Permanent	Paper
Shipping 	Shipping/Name Badge Labels	S0722430	54 x 101	220 x 1	Permanent	Paper
	High Capacity Shipping Labels	S0947420	102 x 59	575 x 2	Permanent	Paper
	Shipping/Name Badge Labels	2093092	54 x 101	220 x 6	Permanent	Paper
	Shipping/Name Badge Labels	S0722420	54 x 101	220 x 12	Permanent	Paper
	Extra Large Shipping Labels	S0904980	104 x 159	220 x 1	Permanent	Paper
	Shipping/Name Badge Labels (Yellow)	2133400	54 x 101	220 x 1	Permanent	Paper
	Shipping/Name Badge Labels (Red)	2133399	54 x 101	220 x 1	Permanent	Paper
Multi-Purpose 	Multi-Purpose Labels	S0722530	13 x 25	1,000 x 1	Removable	Paper
	Square Multi-Purpose Labels	S0929120	25 x 25	750 x 1	Removable	Paper
	Multi-Purpose Labels	S0722550	19 x 51	500 x 1	Removable	Paper
	Multi-Purpose Labels	S0722540	32 x 57	1,000 x 1	Removable	Paper
	Large Multi-Purpose Labels	S0722440	54 x 70	320 x 1	Permanent	Paper
	Large Multi-Purpose Labels	2093094	32 x 57	1,000 x 6	Permanent	Paper
	Large Multi-Purpose Labels	2093095	32 x 57	1,000 x 12	Permanent	Paper
Specialty 	Suspension File Labels	S0722460	12 x 50	220 x 1	Permanent	Paper
	LAF Labels (Small)	S0722470	38 x 190	110 x 1	Permanent	Paper
	LAF Labels (Large)	S0722480	59 x 190	110 x 1	Permanent	Paper
	Name Badge Labels (Small)	S0722560	41 x 89	300 x 1	Removable	Paper
	Appointment/Name Badge Cards	S0929100	51 x 89	300 x 1	Non-adhesive	Paper



Industrial
strength
adhesive



Moisture
resistant



Solvent
resistant



Temperature
rating:
-18°-50° C



No ink
or toner

LabelWriter™
Durable Labels

Style	Item #	Size (mm)	Labels x Roll/Box	Adhesive	Material
SANITIZER	2112283	25 x 54	160 x 1	Permanent	Coated Polypropylene
	2112284	19 x 64	450 x 2	Permanent	Coated Polypropylene
	2112285	25 x 89	350 x 1	Permanent	Coated Polypropylene
	2112286	25 x 25	850 x 2	Permanent	Coated Polypropylene
	2112287	104 x 159	200 x 1	Permanent	Coated Polypropylene
	2112288	59 x 190	170 x 1	Permanent	Coated Polypropylene
	2112289	57 x 32	800 x 1	Permanent	Coated Polypropylene
	2112290	59 x 102	300 x 1	Permanent	Coated Polypropylene



This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

© 2021 Newell Office Brands