


6 Outlet White Power Strip with 270 joules Surge Protection

multicomp PRO

Wire Construction



Copper	No of conductors	3
	AWG	14 AWG
	Stranding (No of wire x wire ga.)	42 x 0.25mm
Overall Jacket	Compound Requirement	PVC 60°C Insulation Compound Approved for SJT Cable
	Jacket Construction	100% Fully Pressure Extruded Jacket (No tube jacketing)
	Colour	Black and Grey
	Indent Marking	(UL) SJT 3X14AWG 60°C 300V VW-1 c(UL) SJT 3X2.08mm ² (14AWG) FT2 60°C 300V
	Conductor Pattern	

Technical Specifications

Housing	Outlets	Total Quantity Standard: 6
	Material	ABS
Male Plug	Male Blades-Nickel Plated Brass	One Hot and One Neutral Male Blades for NEMA 5-15P
	Male Ground-Nickel Plated Brass	One Male Ground Pin for NEMA 5-15P
	Male Plug:	Straight
Approvals	Agency Approval	UL
	UL Standard Reference Number	e302504
Electrical	Rated For	Indoor Use
	Electrical Ratings	15 Amps; 125 Volts; 1875 Watts; 60 Hz
	On/Off Switch	Lighted or Unlighted
	Resettable Circuit Breaker	15A, built into the On/Off Switch
Protection	Joule Rating	270 joules
	Metal-Oxide Varistor (MOV)	Quantity: 1pcs
		Joule Rating per MOV: 270joules
	Voltage Protection Rating (VPR)	500V
Auto-shutdown	Yes	

Part Number Table

Description	Part Number
6 Outlet White Power Strip with 270 joules surge protection, 5ft. Cord, Straight Plug	28-21295

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicomp PRO