



32" HD Ready Traveller TV with built-in DVD Player & satellite tuner

- 32" HD Ready Traveller TV
- Built-in DVD Player
- Built-in satellite tuner
- Freeview DVB-T2 Channels
- 12-volt adaptor included
- HDMI x 2 inputs for external devices & consoles
- 16.7 million display colours
- 3000:1 contrast ratio
- VESA 100mm x 100mm

	EAN	5060750400326
General Feature	Model No.	C3220TRAV
	Panel	HV320WHB
	Destination Country	UK
	Screen Size	32" LED panel
	Max. Resolution	1366 x 768 pixels
	Contrast Ratio (Typical)	3000:1
	Brightness (TYP cd/m2)	200
	Display Colors	16.7M
	Viewing Angle H/V	89/89/89/89(CR≥10)
	Cabinet Color	Piano Black
	Wall Mounting Support (Screw Size)	100 x 100mm (M5 x 8)

Reception	TV System	DTV: DVB-C, DVB-S2 & DVB-T2
	5V from Antenna	Yes

Sound	Bass	Yes
	Treble	Yes
	Balance	Yes
	Sound Mode	Standard/music/movie/sports/user
	Stereo System	NICAMA2
	Audio Output	2 x 3W
	Speaker Distortion	≤7% Max
	Speaker Impedance	4ohm

Connectors Jack	RF Antenna	x 2
	HDMI	x 2
	CVBS	x 1(3.5 ϕ Mini Jack)
	PC In	x 1
	Audio In	PC audio x 1(3.5 ϕ Mini Jack) CVBS Audio x1 (Shared with Ypbpr)
	Scart	x 1
	YPbPr	YES x 1(3.5 ϕ Mini Jack)
	Digital Audio out	x 1
	Earphone Out	x 1
	USB on TV	x 1
	CI	x 1

Other Features	APS	ATV, DVBT, DVBC storage in capture order
	OSD Language	English, German, Francais, Espanol, Portugese, Italian
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	YES

Power	Power Supply	DC12V-5A /AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	34W
	Standby Power Consumption	<0.5W
	Energy Efficiency Class	G

Accessories	Remote Control	x 1
	Power Cable	N/A
	Warranty	x 1
	Battery	1.5V (AAA) x 2

Dimensions	Unit Dimension With Stand (mm)	730 x 182 x 483
	Unit Dimension Without Stand (mm)	730 x 94 x 431