



Boxes

mkelectric.co.uk



Moulded Boxes

32MM
SURFACE44MM
SURFACEDRY LINING
35MM
FLUSHMI CABLE BOXES
37MM
SURFACE
2140WHI 10
FOR 1 GANG
POWER ACCESSORIES
SQUARE CORNERS

Knockouts are provided in base and sides for cable entry

DIMENSIONS

 1 gang: 87 x 87mm
2 gang: 87 x 148mm

FIXING CENTRES

 1 gang: 60.3mm
2 gang: 120.6mm
BS 5733:2010

2031WHI 10
FOR 1 GANG
POWER ACCESSORIES
SQUARE CORNERS

Knockouts in base and sides for cable entry.

DIMENSIONS

87 x 87mm

FIXING CENTRES

 60.3mm
BS 5733:2010

QFB1WHI 20
1 GANG
QFB2WHI 10
2 GANG

 All round flange for a flush fit. One piece moulded lug automatically snaps into place. No rear projections. Clamp device on cable entry. Will accommodate partition thickness between 6mm and 16mm. Earth terminal facility.
BS 4662:2006

QFB/IG1 20
1 GANG WITH
INTUMESCENT GASKET
QFB/IG2 10
2 GANG WITH
INTUMESCENT GASKET

QFB/IG1 & QFB/IG2

 Pre-fitted with intumescent gaskets to give fire protection, in accordance with BS 476-2:1987. In a fire situation, a chemical reaction will occur with the intumescent material. The void behind the wiring device will be filled, providing protection against the passage of fire.
BS 4662:2006


K2131WHI 5
1 GANG
10 CLAMPS
K2132WHI 5
2 GANG
12 CLAMPS

Clamps accept 20mm sealing pots.

DIMENSIONS

 1 gang: 92 x 92mm
2 gang: 92 x 152mm

FIXING CENTRES

 1 gang: 60.3mm
2 gang: 120.6mm
BS 5733:2010
DUAL BOX
38MM
SURFACE40MM
SURFACEFLANGE BOXES
45MM
FLUSHMounting
Pattresses
SURFACE
K2025WHI 5
FOR MOUNTING
TWO 1 GANG
LOGIC PLUS™
ACCESSORIES

This box has two slots in base with 60.3mm and 120.6mm fixing centres for fitting over BS 4226 flush boxes. Knockouts provided for cable entry. Includes integral dividing fillet.

 DIMENSIONS
86 x 172 mm
BS 5733:2010

K2031WHI 10
FOR 1 GANG
LOGIC PLUS™
POWER ACCESSORIES
K2172WHI 5
FOR 2 GANG
LOGIC PLUS™ 50 AMP
DP SWITCHES

Knockouts provided in sides and base.

K2172: Earth terminal fitted in base of box.

DIMENSIONS

 K2031: 87 x 87mm
K2172: 87 x 148mm

FIXING CENTRES

 K2031: 60.3mm
K2172: 120.6mm
BS 5733:2010

K2061WHI 5
1 GANG
K2062WHI 5
2 GANG

DIMENSIONS

 K2061: 88 x 88mm
K2062: 88 x 148mm

FIXING CENTRES

 K2061: 60.3mm
K2062: 120.6mm
BS 5733:2010

K2134WHI 10
1 GANG 20MM DEEP
FOR LOGIC PLUS™
ACCESSORIES
K2133WHI 10
2 GANG 20MM DEEP
FOR LOGIC PLUS™
ACCESSORIES

FIXING CENTRES

 1 gang: 60.3mm
2 gang: 120.6mm
BS 5733:2010