

NC 600 Solder Wire –Sn60/Pb40 Solder Wire

No-Clean
QUALITEK®

NC600(No-Clean)

Utilizing synthetically refined resin and a very effective activator, NC600 wets and spreads like an RA type.

NC600 exhibits virtually no splattering. NC600 conforms to QQ-S-571 and J-STD-004.

Alloy Sn60/Pb40

Melting Range 183-190 C

Qualitek® is a trademark of Qualitek International, Inc.

PHYSICAL & CHEMICAL CHARACTERISTICS (FLUX EXTRACT)

NC600		
Color & Appearance	Lt. Opaque Solid	
Softening Point, C $\approx$ (Flux Extract)	75 $\approx$	
Acid Number (mgKOH/g sample)	190-210	
Silver Chromate(Qualitative Halides)	No Detection	
Classification Per J-STD-004	REL0	
Surface Insulation Resistance	>1.0 x 10 ⁹	
Shelf Life	Indefinite	
Residue Removal	Not Required. May be removed with CFC replacement solvent or Qualitek 1005 Saponifier	


STANDARD PACKAGING

Qualitek flux-core wire and solid wire are packed in ½ pound, 1 pound, 1 kilogram, and 5 pound spools. We also offer 50 pound to 250 pound Quali-packs in rugged fiber containers.

STANDARD WIRE DIAMETERS

DIAMETER/INCH	0.125	0.092	0.062	0.050	0.040	0.032	0.025	0.020	0.015	0.010
DIAMETER/MM	3.17	2.3	1.57	1.27	1.01	0.81	0.63	0.50	0.38	0.25
STD.WIRE GAUGE	11	13	16	18	19	21	23	25	28	31

STANDARD FLUX CORE PERCENTAGE*



TEL: +44 (0) 151 334 0888 FAX: +44 (0) 151 346 1408 E-mail: sales@qualitek-europe.com Internet: www.qualitek.com
9 Apex Court, Bassendale Road. Wirral International Business Park, Bromborough, Wirral, CH62 3RE

QUALITEK

WORLDWIDE BRANCHES: UNITED KINGDOM – MEXICO – CHINA – PHILIPPINES – SINGAPORE-USA

This data is based on information that the manufacturer believed to be reliable and offered in good faith. Qualitek International, Inc. makes no warranties expressed or implied as to its accuracy and assumes no responsibilities and liabilities arising out of its use by others as conditions and methods of use of the products is beyond the control of Qualitek International, Inc. The user must determine the suitability of the product before using it on a commercial basis. The warranties extend only to the conformity of the product to the physical descriptions. In no event will Qualitek International, Inc. be responsible for special, incidental and consequential damages whether the claim is in contract, negligence or otherwise.