




Technical Hotline
+44 (0)1268 563720

Aspect

WIRING DEVICES
DECORATIVE

Socket Outlets

1 GANG
DUAL EARTH
13 AMP



2 GANG
DUAL EARTH
13 AMP



1 GANG
ROUND PIN
5 AMP



Shaver/Toothbrush Supply Outlet

DUAL VOLTAGE
OUTPUT 115/230V
INPUT 220/240V
50/60HZ



K24780BSS*	1	K24781BSS*	1	K24381BSS*	1	K24709BSS*	1
K24780LBS*	1	K24781LBS*	1	K24381LBS*	1	K24709LBS*	1
K24780BRC*	1	K24781BRC*	1	K24381BRC*	1	K24709BRC*	1
K24780POC*	1	K24781POC*	1	K24381POC*	1	K24709POC*	1
K24780SAG*	1	K24781SAG*	1	K24381SAG*	1	K24709SAG*	1
K24780WHIW	1	K24781WHIW	1	K24381WHIW	1	K24709WHIW	1
K24780LIVW	1	K24781LIVW	1	K24381LIVW	1	K24709LIVW	1
K24780LBKB	1	K24781LBKB	1	K24381LBKB	1	K24709LBKB	1
K24780PBR*	1	K24781PBR*	1	K24381PBR*	1	K24709PBR*	1
K24780TIRB	1	K24781TIRB	1	K24381TIRB	1	K24709TIRB	1
K24780DBZB	1	K24781DBZB	1	K24381DBZB	1	K24709DBZB	1
K24780ABSB	1	K24781ABSB	1	K24381ABSB	1	K24709ABSB	1
K24780TCOB	1	K24781TCOB	1	K24381TCOB	1	K24709TCOB	1

* Available with the option of either White or Black inserts. Add Suffix 'W' or 'B' to part number when ordering, E.g. KxxxxBSSW.
Where there is no asterisk, the final suffix W = White Insert, B = Black Insert, E.g. KxxxxWHIW = Porcelain White finish with White inserts

MOUNTING BOXES

FLUSH 35MM

866ZIC

FLUSH 46MM

877ZIC (for extra wiring space)

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

BS 1363-2:1995

MOUNTING BOXES

FLUSH 35MM

886ZIC

FLUSH 47MM

878ZIC (for extra wiring space)

DIMENSIONS

86 x 146mm

FIXING CENTRES

120.6mm

BS 1363-2:1995

MOUNTING BOXES

FLUSH 35MM

866ZIC

FLUSH 46MM

877ZIC (for extra wiring space)

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

BS 546:1950

MOUNTING BOXES

FLUSH

878ZIC

This design incorporates a double wound isolating transformer rated 20VA at 230 or 115 volts and meets BS EN 61558-2-5: 1998 making it safe for use in bathrooms.

Insertion of a shaver/toothbrush plug automatically switches on by energising the primary side of the isolating transformer – removal automatically switches off. The transformer is protected against overload by an automatic solid state overload device with automatic resetting.

DIMENSIONS

146 x 86mm

FIXING CENTRES

120.6mm

BS EN 61558-2-5:1998

Dual Earth: Fitted with two earth terminals to provide a double earth facility for use when installations require a high integrity protective connection as specified within BS 7671: 2008.