



Technical Hotline
+44 (0)1268 563720

Logic Plus™


WIRING DEVICES
WHITE

Plateswitches

NEON LOCATOR



Neon locator on a
plateswitch



K3041

FLUSH
10 AMP



K4870GRA



K4871WHI



K4872WHI



K4872GRA


FLUSH
10 AMP




K4875WHI



K4873WHI



K4874WHI



K4879WHI

FLUSH
20 AMP



K4870D2WHI



K4871D2WHI



K4872D2WHI



K4873D2WHI

FLUSH
10 AMP



K4878BWHI



K4878PWHI

K3041 5
NEON PLATESWITCH
LOCATOR
200-250V, 50HZ.
TUNGSTEN GLS LAMPS ONLY

Neon Plateswitch Locator is for use
with any 1, 2 and 3 GANG Logic Plus™
plateswitches.
Used for location of switches in dark
situations.
FIXING CENTRES
60.3mm
BS 5733:2010

K4870WHI 10
K4870GRA 10
1 GANG SP
ONE-WAY
K4871WHI 10
K4871GRA 10
1 GANG SP
TWO-WAY
K4872WHI 10
K4872GRA 10
2 GANG SP
TWO-WAY

MOUNTING BOXES
FLUSH

1, 2 & 3 GANG: 861ZIC
4 & 6 GANG: 862ZIC

SURFACE

1, 2 & 3 GANG: K2160WHI
4 & 6 GANG: K2161WHI

These switches do not have to be
derated when used with fluorescent or
inductive loads.

K4871, K4872, K4873,
K4874, K4879

These switches can be wired as either
one-way or two-way.

K4875WHI 10
1 GANG
INTERMEDIATE
K4876WHI 10
1 GANG DP
ONE-WAY
K4873WHI 10
3 GANG SP
TWO-WAY
K4874WHI 5
4 GANG SP
TWO-WAY
K4879WHI 5
6 GANG SP
TWO-WAY

DIMENSIONS

1, 2 & 3 GANG: 86 x 86mm
4 & 6 GANG: 86 x 146mm

FIXING CENTRES

1, 2 & 3 GANG: 60.3mm
4 & 6 GANG: 120.6mm

BS EN 60669-1:1999

K4870D2WHI 10
1 GANG SP
ONE-WAY
K4871D2WHI 10
1 GANG SP
TWO-WAY
K4872D2WHI 10
2 GANG SP
TWO-WAY
K4873D2WHI 10
3 GANG SP
TWO-WAY
K4874D2WHI 5
4 GANG SP
TWO-WAY
K4875D2WHI 10
1 GANG INTERMEDIATE

MOUNTING BOXES

FLUSH

861ZIC

SURFACE

K2160WHI

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

K4878BWHI 10
1 GANG SP
TWO WAY
PUSH SWITCH WITH
BELL SYMBOL
PUSH TO MAKE OR
BREAK
K4878PWHI 10
1 GANG SP
TWO WAY
PUSH SWITCH MARKED
'PRESS'
PUSH TO MAKE OR BREAK

MOUNTING BOXES

FLUSH

861ZIC

SURFACE

K2160WHI

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

BS EN 60669-1:1999