

## TV/FM and Satellite Co-Axial Socket Outlets

NON ISOLATED  
FLUSH

ISOLATED  
FLUSH



K3520WHI



K3523WHI



K3525WHI



K3525D1WHI



K3521WHI



K3522WHI



K3631GRA



K3632WHI




K3633GRA




K3634WHI



K3636WHI



K3638WHI



K3639WHI

**K3520WHI** 10  
SINGLE OUTLET

**K3523WHI** 10  
TWIN OUTLET

**K3525WHI** 10  
SINGLE F TYPE  
SATELLITE SOCKET

**K3525D1WHI** 10  
TWIN F TYPE  
SATELLITE SOCKET

**MOUNTING BOXES**  
FLUSH  
861ZIC (25mm)  
SURFACE  
K2140WHI

Single outlet for connection to a single TV or FM co-axial aerial lead. Twin outlet for connection to each of two separate TV/FM, co-axial aerial leads.

**DIMENSIONS**  
86 x 86mm  
**FIXING CENTRES**  
60.3mm  
BS 5733:2010 where applicable  
BS 3041:1977  
IEC 169-2:1965

**K3521WHI** 10  
SINGLE OUTLET

**K3522WHI** 10  
TWIN OUTLET  
WITH FM/TV DIPLEXER

**MOUNTING BOXES**  
FLUSH  
861ZIC (25mm)  
SURFACE  
K2140WHI

Provides safety isolation rated at 2000Va.c. between aerial lead and socket.  
Single outlet for connection to a single TV or FM co-axial aerial lead.  
Twin outlet with TV/FM diplexer for connection to single co-axial aerial lead with combined TV & FM signals.

**DIMENSIONS**  
86 x 86mm  
**FIXING CENTRES**  
60.3mm  
BS 5733:2010 where applicable  
BS 3041:1977 IEC 169-2:1965

**K3631WHI** 10  
**K3631GRA** 10  
1 MODULE

**K3632WHI** 10  
**K3632GRA** 10  
2 MODULE

**K3633WHI** 10  
**K3633GRA** 10  
3 MODULE

**K3634WHI** 10  
**K3634GRA** 10  
4 MODULE

All modules from the Grid Plus range can be used with these frontplates.

**DIMENSIONS**  
1 & 2 MODULE: 86 x 86mm  
3 & 4 MODULE: 86 x 146mm  
6 & 8 MODULE: 146 x 146mm  
12 MODULE: 206 x 146mm  
BS 5733:2010

**K3636WHI** 1  
**K3636GRA** 1  
6 MODULE

**K3638WHI** 1  
**K3638GRA** 1  
8 MODULE

**K3639WHI** 1  
12 MODULE