



Technical Hotline
+44 (0)1268 563720

Logic Plus™

WIRING DEVICES
WHITE

Multimedia Plates

FLUSH
13 AMP



K2741WHI 1
2 GANG DP
COMBINATION PLATE
WITH 4 X EURO APERTURE
K2740WHI 1
4 GANG DP
COMBINATION PLATE WITH
TV/FM/DAB/SAT X 2 QUAD,
TV, TELEPHONE AND
4 X EURO APERTURE

MOUNTING BOXES

FLUSH 35MM
2 GANG: 857ZIC*
4 GANG: 853ZIC*
FLUSH 47MM

2 GANG: 858ZIC*
4 GANG: 854ZIC*

DIMENSIONS

K2741: 173 x 146mm
K2740: 173 x 294mm
BS 1363 Pt 2:1995

*Provides segregation between power and TV/FM/SAT/DAB/
Euro Module sections

Switchsocket Outlets

NON STANDARD
FLUSH
13 AMP



K1257WHI 10
1 GANG DP
K1246WHI 5
2 GANG DP
K1257D1WHI 10
1 GANG DP
WITH RED ROCKER
K1246D1WHI 5
2 GANG DP
WITH RED ROCKERS
K1246D1RED 5
2 GANG DP
WITH RED FRONTPLATE
AND RED ROCKERS

MOUNTING BOXES

FLUSH 25MM

1 GANG: 861ZIC
2 GANG: 862ZIC

FLUSH 35MM (for extra wiring space)
1 GANG: 866ZIC, 2 GANG: 886ZIC

SURFACE

1 GANG: K2140WHI, 2 GANG: K2142WHI

These products are provided with facilities for 'clean earth'
connection and are suitable for non standard plugs with 'T'
shaped earth pin. See page 240.

DIMENSIONS

1 GANG: 86 x 86mm
2 GANG: 86 x 146mm

FIXING CENTRES

1 GANG: 60.3mm
2 GANG: 120.6mm

BS 1363 Pt 2:1995 where relevant

ROUND PIN
FLUSH



K2891WHI 10
1 GANG
5A DP SHUTTERED
K2893WHI 10
1 GANG
15A DP SHUTTERED
K2493WHI 10
1 GANG
15A DP SHUTTERED
WITH NEON

MOUNTING BOXES

FLUSH

861ZIC (25mm)
866ZIC (35mm for extra wiring space)

SURFACE

K2140WHI

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

BS 546:1950