



Technical Hotline
+44 (0)1268 563720

Metalclad Plus™

WIRING DEVICES
SURFACE

Switches

UNSWITCHED
FUSED
13 AMP

10 AMP



K932ALM



K972ALM



K972D6ALM



K3072WHI



K954ALM



K983ALM



K989ALM



K986ALM



K3054WHI



K3086WHI



K3591ALM



K3592ALM



K3593ALM



K5252ALM



K3091WHI



K3092WHI

K932ALM
DP SWITCHED
WITH FLEX OUTLET
K972ALM
DP SWITCHED
WITH FLEX OUTLET
AND NEON
K972D6ALM
DP SWITCHED
WITH FLEX OUTLET,
NEON AND RED ROCKER
K3072WHI
DP SWITCHED
WITH FLEX OUTLET
AND NEON
WITHOUT BOX

5 **K954ALM**
UNSWITCHED
5 **K983ALM**
UNSWITCHED WITH NEON
5 **K989ALM**
UNSWITCHED
WITH FLEX OUTLET
1 **K986ALM**
UNSWITCHED
WITH FLEX OUTLET AND NEON
10 **DIMENSIONS**
86 x 86 x 47mm
KNOCKOUTS
6 x 20mm.
Two in one side and one in each
of other three sides, one in base.
Spare Boxes with and without
knockouts are available.
All boxes have a base knockout.
BS 1363-4:1995

5 **K3054WHI**
UNSWITCHED
WITHOUT BOX
5 **K3086WHI**
UNSWITCHED WITH
FLEX OUTLET AND NEON
WITHOUT BOX
5 **MOUNTING BOX**
1 gang K829ALM* K899ALM
(*without side knockouts)
All boxes have a base knockout

10 **K3591ALM**
1 GANG SP
TWO WAY
10 **K3592ALM**
2 GANG SP
TWO WAY
K3593ALM
3 GANG SP
TWO WAY
K5252ALM
20AX DP KEY
OPERATED SWITCH

DIMENSIONS
Key Operated: 86 x 86 x 51mm
Switch: 86 x 86 x 47mm
SPARE BOXES
1 gang K829ALM* K899ALM
(*without side knockouts)
All boxes have a base knockout.
BS 5733:2010
SOCKET
BS 1363-2:1995
SWITCH
BS EN 60669-1:1999
These switches do NOT have to be
derated when used with fluorescent or
inductive loads.
An earth terminal is fitted in each box.
KNOCKOUTS
6 x 20mm
Two in one side and one in each
of other three sides, one in base.
BS EN 60669-1:1999

5 **K3091WHI**
1 GANG SP
TWO WAY
WITHOUT BOX
5 **K3092WHI**
2 GANG SP
TWO WAY
WITHOUT BOX
5 **MOUNTING BOX**
1 gang K829ALM* K899ALM
(*without side knockouts)
All boxes have a base knockout