

Albany Plus™

Blank Plates

1 GANG



2 GANG



TV/FM Coaxial Socket Outlets

NON ISOLATED



ISOLATED

TWIN OUTLET
WITH TV/FM
DIPLEXER

FINISHES	1 GANG		2 GANG		NON ISOLATED	ISOLATED	TWIN OUTLET WITH TV/FM DIPLEXER	
BRUSHED STAINLESS STEEL	K3330BSS	10	K3329BSS	5	K3580BSS	5	K3582BSS	5
BRUSHED CHROME	K3330BRC	1	K3329BRC	1	K3580BRC	1	K3582BRC	1
SATIN GOLD	K3330SAG	1	K3329SAG	1	K3580SAG	1	K3582SAG	1
POLISHED CHROME	K3330PCR	1	K3329PCR	1	K3580PCR	1	K3582PCR	1

LEAD TIMES
Please contact our Customer
Services Department on
01268 563 404

MOUNTING BOXES
FLUSH
1 gang: 86ZIC
SURFACE
WITH KNOCKOUTS
1 gang: K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS 5733:2010

MOUNTING BOXES
FLUSH
2 gang: 88ZIC
SURFACE
WITH KNOCKOUTS
2 gang: K897ALM
SURFACE WITHOUT
KNOCKOUTS
K830ALM
DIMENSIONS
86 x 146mm
FIXING CENTRES
120.6mm
BS 5733:2010

MOUNTING BOXES
FLUSH
861ZIC
SURFACE
WITH KNOCKOUTS
K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
K3580
Single outlet for connection
to a single TV or FM co-axial
aerial lead

MOUNTING BOXES
FLUSH
861ZIC
SURFACE
WITH KNOCKOUTS
K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
K3581
Provides safety isolation rated
at 2000V a.c. between aerial
lead and socket. Single outlet
for connection to a single TV
or FM co-axial aerial lead

MOUNTING BOXES
FLUSH
861ZIC
SURFACE
WITH KNOCKOUTS
K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
K3582
Provides safety isolation rated
at 2000V a.c. between aerial
lead and socket. Single outlet
for connection to a single TV
or FM co-axial aerial lead. Twin
outlet with TV/FM