

## Telephone Socket Outlets

FLUSH



K422WHI



K427WHI



K4817WHI



K3540WHI

## TV/FM and Satellite Co-Axial Socket Outlets

FOR DIGITAL AND INTERACTIVE SERVICES  
SCREENED, NON ISOLATED  
FLUSH



K3550WHI



K3551WHI



K3555WHI



K3552WHI



K3552DABWHI



K3553WHI



K3553DABWHI



K3554DABWHI

- K422WHI** 10  
1 GANG  
TELEPHONE MASTER
- K427WHI** 10  
1 GANG  
TELEPHONE SECONDARY
- K4817WHI** 10  
1 GANG  
RJ11 TELEPHONE SOCKET
- K3540WHI** 10  
3 PIN WITH  
TELEPHONE SYMBOL  
(NON UK)
- 400NAT** 10  
IDC INSERTION TOOL

BS 6312 Pt 2  
K4817 FCC 68  
K3540  
Accepts standard BS 546  
2A 2 pin and earth plug where 2 pins are  
used for telephone circuits and the earth  
pin is used to ensure correct polarity.  
BS 546:1950 where applicable

- K3550WHI** 1  
SINGLE OUTLET  
(IEC MALE)
- K3551WHI** 5  
SINGLE OUTLET  
(IEC FEMALE)
- K3555WHI** 1  
SINGLE OUTLET  
F-TYPE SATELLITE SOCKET
- K3552WHI** 5  
TWIN TV/FM  
DIPLEXER

Fully screened non isolated TV outlets  
containing a combination of single,  
TV/FM Diplexer, TV/FM/SAT Triplexer  
and secondary telephone outlets for  
use within digital TV systems and  
interactive TV services.

- K3552DABWHI** 1  
TWIN TV/FM  
DAB DIPLEXER
- K3553WHI** 5  
TRIPLE TV/FM/SAT  
TRIPLEXER
- K3553DABWHI** 1  
TRIPLE TV/FM DAB/SAT  
TRIPLEXER
- K3554DABWHI** 1  
QUAD TV/FM DAB/SATX2  
QUADPLEXER

Single outlets for connection to a single  
TV, FM or Satellite co-axial aerial lead.  
TV/FM diplexer units for connection to a  
single co-axial aerial lead with combined  
TV and FM signals.

### MOUNTING BOXES

Minimum box depth 32mm		
1 GANG:	Flush:	866ZIC
	Surface:	K2181WHI
2 GANG:	Flush:	886ZIC
	Surface:	K2183WHI

### DIMENSIONS

1 GANG:	86 x 86mm
2 GANG:	86 x 146mm

### FIXING CENTRES

1 GANG:	60.3mm
2 GANG:	120.6mm

### PERFORMANCE

Refer to page 474 for technical  
specification.