

## Product information

# 98 99 12

### Standard Tool Case

26 parts

With insulated tools for works on electrical installations

IEC 60900 DIN EN 60900

- Shock-resistant plastic case
- Equipped with a range of insulated KNIPEX tools for works on electrical installations
- Foam inserts with recesses for the tools
- Fixable partition wall
- Dimensions, exterior (W x H x D): 440 x 105 x 385 mm



⚡ 1000V

### General

Article No.	98 99 12
EAN	4003773026631
Weight	4,710 g
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

### Technical details






























Inside compartments	26 pcs
---------------------	--------

### Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076
UNSPSC 13.1	24113106

### Content

03 07 200	1 x Combination Pliers ⚡ 1000V  
70 07 160	1 x Diagonal Cutter ⚡ 1000V 

Content	
98 00 10	1 x Open-end wrench (10 mm) ⚡1000V 
98 00 11	1 x Open-end wrench (11 mm) ⚡1000V 
98 00 12	1 x Open-end wrench (12 mm) ⚡1000V 
98 00 13	1 x Open-end wrench (13 mm) ⚡1000V 
98 00 14	1 x Open-end wrench (14 mm) ⚡1000V 
98 00 17	1 x Open-end wrench (17 mm) ⚡1000V 
98 00 19	1 x Open-end wrench (19 mm) ⚡1000V 
98 20 25	1 x Screwdrivers for slotted screws (2,5 mm) ⚡1000V 
98 20 35	1 x Screwdrivers for slotted screws (3,5 mm) ⚡1000V 
98 20 40	1 x Screwdrivers for slotted screws (4,0 mm) ⚡1000V 
98 20 55	1 x Screwdrivers for slotted screws (5,5 mm) ⚡1000V 
98 24 00	1 x Screwdriver for cross recessed screws Phillips® (PH0) ⚡1000V 
98 24 01	1 x Screwdriver for cross recessed screws Phillips® (PH1) ⚡1000V 
98 24 02	1 x Screwdriver for cross recessed screws Phillips® (PH2) ⚡1000V 
98 40	1 x T-Handle Drive with driving square 1/2" ⚡1000V 
98 47 10	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (10 mm) ⚡1000V  
98 47 11	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (11 mm) ⚡1000V  
98 47 12	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (12 mm) ⚡1000V  
98 47 13	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (13 mm) ⚡1000V  
98 47 14	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (14 mm) ⚡1000V  
98 47 17	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (17 mm) ⚡1000V  
98 47 19	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (19 mm) ⚡1000V  



**Content**

98 52	1 x Cable Knife ⚠1000V
98 53 03	1 x Stripping Knives ⚠1000V

*technical change and errors excepted*