

CONNECTORS (Cont.)



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



~~Fig. 8~~



Fig. 9



Fig. 10



~~Fig. 11~~



Fig. 12



Fig. 13



Fig. 14



Fig. 15



Fig. 16

BNC Adapters

Retail Part No.	Bulk Part No.	Figure Number	Description	Quantity Per Retail Pack
33-1102	33-1102-BU	1	Right Angle BNC Male to BNC Female	1
33-1195	33-1195-BU	2	BNC Double Male	2
33-1196	33-1196-BU	3	BNC "T", 1 Male, 2 Female	1
33-1197	33-1197-BU	4	BNC "T", 3 Female, 50Ω	1
	33-1199-BU	5	BNC, 4 Female	
33-1555	33-1555-BU	6	BNC Female to "N" Male	1
32-3109	32-3109-BU	7	BNC Male to RCA Female	1
32-3115	32-3115-BU	8	BNC Male to UHF Female	1
	32-3116-BU	9	BNC Male to "N" Male	
32-3117	32-3117-BU	10	BNC Male to "N" Female	1
	32-3118-BU	11	BNC Female to UHF Male	
32-3119	32-3119-BU	12	BNC Double Female	2
32-3121	32-3121-BU	13	BNC Female to RCA Male	1
	32-3122-BU	14	BNC Female to UHF Female	
32-3123	32-3123-BU	15	BNC 3 Male	1
32-3190	32-3190-BU	16	BNC Male to TNC Female	1



Fig. 17



Fig. 18



Fig. 19

BNC Chassis Mount Bulkhead

Retail Part No.	Bulk Part No.	Figure Number	Description	Cable Type
	33-1106-BU	17	BNC Female to Female Chassis Mount, 1/2" Mount Hole	
	33-1231-BU	18	BNC Female Chassis Mount, 3/8" Mount Hole	
	33-1232-BU	19	BNC Female Chassis Mount, Insulated, 3/8" Mount Hole	



Fig. 20

BNC Terminators

Retail Part No.	Bulk Part No.	Figure Number	Description	Cable Type
	33-1175-BU	20	BNC 75 Ohm	
	33-1176-BU	20	BNC 50 Ohm	
	33-1177-BU	20	BNC 93 Ohm	



Fig. 21



Fig. 22



Fig. 23

"N" Connectors

Retail Part No.	Bulk Part No.	Figure Number	Description	Use with GC Wire Part No.	Cable Type
	32-3112-BU	21	Male Crimp, 3-Piece Set	14-1924-9H81	RG-59/RG-62
	33-1510-BU	21	Male Crimp, 3-Piece Set		RG-8/RG-11/RG-213/RG-214
	33-1500-BU	22	Male Compression, 6-Piece		RG-8/RG-213/RG-214
	32-3124-BU	23	Male Clamp Type		RG-58
	32-3125-BU	23	Male Clamp Type	14-1924-9H81	RG-59/RG-62