

Product information

00 21 19 LB S

KNIPEX L-BOXX® Plumbing

52 parts



Ideal storage and transport solution: the KNIPEX L-BOXX® with a large range of tools for the plumbing, heating and air-conditioning professional

- Strong box made of impact- and shock-proof ABS plastic
- Equipped with 13 KNIPEX tools, a total of 52 brand tools, partly VDE-tested according to DIN EN 60900
- Max. payload: 25 kg
- Splash-proof
- Several boxes can be securely joined together
- Flexible inner partitions
- Handle can be lowered into a hollow in the lid to save space
- Ergonomically shaped handles with additional moulded recess on the side for flexible, convenient handling
- With two-piece tool board made from dirt-repellent PP twin-wall sheets
- Tool boards are connected to each other using hook-and-loop
- Top section with 10 pockets and 10 elastic straps
- Upper part of bottom section with 7 pockets and strap for hanging up the tool board; can also be used to lift or lay the KNIPEX L-BOXX® down
- Bottom of base part with 7 pockets and 7 elastic straps
- External dimensions (W x H x D): 442 x 357 x 151 mm; internal dimensions (W x H x D): 375 x 107 x 311 mm

General

Article No.	00 21 19 LB S
EAN	4003773081630
Weight	9,170 g
Reach	no
RohS	no






Technical details



Dimension exterior (interior) width mm	442 mm (375 mm)
Dimension exterior (interior) height mm	151 mm (107 mm)
Dimension exterior (interior) depth mm	442 mm (311 mm)

Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076
UNSPSC 13.1	27112117

Content

00 11 01	1 x KNIPEX TwinKey® Control Cabinet Key for all standard cabinets and shut-off systems
26 16 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ⚠️ 1000V   
74 06 180	1 x High Leverage Diagonal Cutter ⚠️ 1000V 
86 03 250	1 x Pliers Wrench pliers and a wrench in a single tool 

Content	
87 01 250	1 x KNIPEX Cobra® High-tech Water Pump Pliers 
87 01 400	1 x KNIPEX Cobra® XL Pipe Wrench and Water Pump Pliers 
98 20 35	1 x Screwdrivers for slotted screws (3,5 mm) ⚠️ 1000V ⚡
98 20 55	1 x Screwdrivers for slotted screws (5,5 mm) ⚠️ 1000V ⚡
98 24 01	1 x Screwdriver for cross recessed screws Phillips® (PH1) ⚠️ 1000V ⚡
98 24 02	1 x Screwdriver for cross recessed screws Phillips® (PH2) ⚠️ 1000V ⚡
98 26 15	1 x Screwdriver for Torx® screws (TX15) ⚠️ 1000V ⚡
98 26 20	1 x Screwdriver for Torx® screws (TX20) ⚠️ 1000V ⚡
98 26 25	1 x Screwdriver for Torx® screws (TX25) ⚠️ 1000V ⚡
16640003	1 x Heyco Safety cutter knife (18 mm)
90958	1 x Heyco Express key (M 10)
0030312-0300	1 x Picard Locksmith's hammer (300 g)
101-0300	1 x Picard Locksmith's hammer (300 g)
71510-000	1 x Picard Metre ruler (yardstick) (2 m)
340 250 1	1 x Rennsteig Mason's Chisels (250 mm)
361 252 1	1 x Rennsteig Electrician's Chisel (250 x 10 mm)
2281	1 x Stabila spirit level type 70 (30 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm)
003760	1 x Wera Joker open-end wrench (10 x 13 mm)
004018	1 x Wera 8100 SA 8 Zyklop set of metal ratchets 28 parts (1/4")
005655	1 x Wera Voltage detector, single-pole 247 (0,5 x 3,0 x 70 mm)
6135-0	1 x Zenten Pipe cutter (3 - 35 mm / 1/8 - 1 1/2")

Accessories	
00 21 19 LB	KNIPEX L-BOXX® empty,
00 21 19 LB WK	Tool board for KNIPEX L-BOXX®,
00 21 19 LB LE	KNIPEX L-BOXX® empty,

technical change and errors excepted

L-BOXX® is a registered trademark of Sortimo International GmbH