

Product information

98 99 11

Compact Tool Case

17 parts

With insulated tools for works on electrical installations

IEC 60900 DIN EN 60900

- Shock-resistant plastic case
- Foam insert with precise recesses for holding the pliers
- Equipped with a range of customary insulated KNIPEX tools for work on electrical systems
- All tools are tested one by one and meet the requirements of ASTM F1505 and IEC 60900.
- Dimensions, exterior (W x H x D): 380 x 85 x 260 mm
- Dimensions, interior (W x H x D): 335 x 70 x 230 mm





























⚡ 1000V

General	
Article No.	98 99 11
EAN	4003773026624
Weight	4,055 g
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details	
Inside compartments	17 pcs

Classification	
eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076
UNSPSC 13.1	24113106

Content	
03 07 200	1 x Combination Pliers ⚡ 1000V  
70 07 160	1 x Diagonal Cutter ⚡ 1000V 

Content	
98 20 35	1 x Screwdrivers for slotted screws (3,5 mm) ⚠️ 1000V 
98 20 40	1 x Screwdrivers for slotted screws (4,0 mm) ⚠️ 1000V 
98 20 55	1 x Screwdrivers for slotted screws (5,5 mm) ⚠️ 1000V 
98 24 00	1 x Screwdriver for cross recessed screws Phillips® (PH0) ⚠️ 1000V 
98 42	1 x Reversible Ratchet with driving square 1/2" ⚠️ 1000V 
98 45 125	1 x Extension Bar with internal/external square 1/2" ⚠️ 1000V  
98 45 250	1 x Extension Bar with internal/external square 1/2" ⚠️ 1000V  
98 47 10	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (10 mm) ⚠️ 1000V  
98 47 11	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (11 mm) ⚠️ 1000V  
98 47 12	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (12 mm) ⚠️ 1000V  
98 47 13	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (13 mm) ⚠️ 1000V  
98 47 14	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (14 mm) ⚠️ 1000V  
98 47 17	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (17 mm) ⚠️ 1000V  
98 47 19	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (19 mm) ⚠️ 1000V  
98 52	1 x Cable Knife ⚠️ 1000V

technical change and errors excepted