



Description

Ultra compact sound level meter measures less than 6" in length, including the windscreen, and provides full 40 ~ 130dB measuring range. Perfect for numerous types of measurement including sound system testing and noise level monitoring.

Features

- Simple one-button operation
- Selectable MIN/MAX hold
- Large 3/4" digit LCD backlit display
- Threaded insert which accepts standard tripod mount
- Auto power off
- 1999 count display with 0.1dB resolution
- Removable windscreen
- Includes manual and 9V battery

Specifications

Frequency Range	: 31.5Hz ~ 8kHz
Measuring Level Range	: 40dB ~ 130dB
Frequency Weighting	: A
Microphone	: 1/2 inch electret condenser
Display	: LCD
Digital Display	: 4 digits, 1999 count Resolution: 0.1dB Refresh Rate: 0.5 sec.
Time Weighting	: 125mS
Accuracy	: ± 3.5dB @1kHz, 94dB (under reference conditions)
Alarm Function	: Displays "OVER" when input exceeds 130dB
Auto power off	: After approximately 15 minutes of inactivity
Power Supply	: One 9V battery, 006P or IEC 6F22 or NEDA 1604
Operation Temperature	: 0 ~ 40°C (32 ~ 104°F)
Operation Humidity	: 10 ~ 90% RH
Storage Temperature	: -10°C ~ +60°C (14°F ~ 140°F)
Storage Humidity	: 10 ~ 75% RH
Dimension	: 5-1/4" (L) × 2" (W) × 1-1/4" (D)
Weight	: 135g (including battery)
Included Accessories	: 9V battery, instruction manual

Part Number Table

Description	Part Number
Compact Digital Sound Level Meter	MP780902

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.