

Capacities	Performance
32GB-1TB*	C10, U1, A1 Up to 120MB/s read**
16GB	C10, A1 Up to 98MB/s read**

SanDisk Ultra® microSDHC™ and microSDXC™ UHS-I Cards

Highlights

- Ideal for Android™ smartphones and tablets, and MIL cameras
- Up to 1TB* to store even more hours of Full HD video²
- Up to 120MB/s** transfer speeds let you move up to 1000 photos in a minute⁵
- [32GB-1TB]**
- Load apps faster with A1-rated performance¹
- Class 10 for Full HD video recording and playback²
- SanDisk® Memory Zone™ app for easy file management⁴

Fast for better pictures, app performance and Full HD video²

The SanDisk Ultra® microSD™ UHS-I card gives you the freedom to shoot, save and share more than ever before. With capacities up to 1TB*, our SanDisk Ultra microSD card is perfect for recording and watching Full HD video,² with room for even more hours of video. Transfer speeds of up to 120MB/s** help you move your content blazingly fast—up to 1000 photos in just one minute.⁵ Ideal for Android™-based smartphones and tablets, this card's A1 rating means that you can load apps faster too.¹

Load Apps Faster with A1-rated performance¹

Rated A1, the SanDisk Ultra® microSD™ card is optimized for apps, delivering faster app launch and performance that provides a better smartphone experience.

SanDisk® Memory Zone™ App for Easy File Management

Available from the Google Play™ store, the SanDisk® Memory Zone™ app lets you view, access, and back up your phone's files in one location. It can also automatically move files from your device to your memory card to free up space.⁴

Compatible with MobileMate® USB 3.0 Reader⁶

Use with the MobileMate® USB 3.0 microSD™ card reader so you can move big files fast, move a lot of files fast or just make frequent file transfers that much quicker.




Technical Specifications

Form Factor	microSDHC™ and microSDXC™
Available Capacity	16GB, 32GB, 64GB, 128GB, 200GB, 256GB, 400GB, 512GB, and 1TB*
Performance/Speed	32GB-1TB: Up to 120MB/s** read speed; write speed lower 16GB: Up to 98MB/s** read speed; write speed lower
Dimensions	microSD™: 0.59in x0.43in x0.03in (14.99mm x 10.92mm x 1.02mm) SD™ adapter: 1.26in x 0.94in x 0.08in (24mm x 32mm x 2.1mm)
Operating Temperature	-13°F to 185°F (-25°C to 85°C)
Storage Temperature	-40°F to 185°F (-40°C to 85°C)
Compatibility	Compatible with all microSDHC and microSDXC supporting host devices
Warranty	10-year warranty ⁷ US only: 10 year limited warranty ⁷

CLASS 10

FULL HD
VIDEO

A1¹
APP PERFORMANCE



For more information, please visit
www.sandisk.com

SanDisk®

At SanDisk®, we're expanding the possibilities of data storage. For more than 25 years, SanDisk's ideas have helped transform the industry, delivering next generation storage solutions for consumers and businesses around the globe.

Western Digital Technologies, Inc.
951 SanDisk Drive | Milpitas | CA 95035 | USA

Western Digital Technologies, Inc. is the seller of record and licensee in the Americas of SanDisk® products.

* 1GB=1,000,000,000 bytes. 1TB=1,000,000,000,000 bytes. Actual user storage less.

** **[for 32GB-1TB]** Up to 120MB/s read speed, engineered with proprietary technology to reach speeds beyond UHS-I 104MB/s, require compatible devices capable of reaching such speed. Write speeds lower. Based on internal testing; performance may be lower depending on host device, interface, usage conditions and other factors. 1MB=1,000,000 bytes.

** **[for 16GB]** Up to 98MB/s read speed; write speed lower. Based on internal testing; performance may be lower depending on host device, interface, usage conditions and other factors. 1MB=1,000,000 bytes.

¹ A1 performance is 1500 read IOPS, 500 write IOPS. Based on internal testing. Results may vary based on host device, app type and other factors.

² Full HD (1920x1080) video support may vary based upon host device, file attributes, and other factors. See: www.sandisk.com/HD.

³ Card only. See www.sandisk.com/proof.

⁴ Download and installation required; see www.sandiskmemoryzone.com.

⁵ Based on internal testing on images with an average file size of 3.55MB (up to 3.7GB total) with USB 3.0 reader. Your results will vary based on host device, file attributes, and other factors.

⁶ Reader not included.

⁷ See www.sandisk.com/wug

SanDisk, the SanDisk logo, Memory Zone, MobileMate, and SanDisk Ultra are registered trademarks or trademarks of Western Digital Corporation or its affiliates in the US and/or other countries. The microSD, microSDHC, and microSDXC marks and logos are trademarks of SD-3C, LLC. Android and Google Play are trademarks of Google LLC. The Android robot is reproduced or modified from work created and shared by Google and used according to terms described in the Creative Commons 3.0 Attribution License. All other marks are the property of their respective owners. ©2020 Western Digital Corporation or its affiliates. All rights reserved. 10/2020