



AUDIO
TECHNOLOGIES®

1/4" PHONE JACKS

TJ SERIES - HORIZONTAL PCB MOUNT

Mono or stereo, horizontal PCB mounted 1/4" phone jacks with switched contacts and a plastic body for audio and control.

Accessory: IO-TJ-NW



IO-TJ6HF

IO-TJ4HF

SPECIFICATIONS

PRODUCT

Gender: **Female**

Contacts: **4 (IO-TJ4HF) or 6 (IO-TJ6HF)**

ELECTRICAL

Contact Resistance: **< 30mΩ**

Insulation Resistance: **≥ 100MΩ**

Dielectric Strength: **500VAC @ 60s**

Current Rating: **1A/30V DC**

Switching Contacts: **3 (N.C.)**

ENVIRONMENTAL

Standard Compliance: **IEC 60603-11**

UL Flammability: **UL94 V-0**

Temperature Range: **-25°C ~ +70° C (-13°F ~ +158°F)**

MECHANICAL

Insertion Force: **5-30N**

Lifetime: **> 5000 Mating Cycles**

Wiring: **Horizontal PCB Mount**

Mounting Direction: **Rear**

Solderability: **Complies with IEC 60068-2-20**

MATERIAL

Contacts: **Brass**

Contact Plating: **.3 μm Ag**

Shell: **PA66**

Shell Finish: **Black**

Nut/Washer: **PBT**

Nut Washer Finish: **Black**


Product specifications may change without prior notification

Io Audio Technologies® is a registered trademark of Knight Electronics, Inc.
10557 Metric Dr. Dallas, TX 75243 | 214-340-0265 | 800-323-2439 | Fax: 214-340-5870 |
www.ioaudiotechnologies.com




DRAWINGS AND SCHEMATICS


IO-TJ4HF



IO-TJ6HF



Panel Cutout



FEATURES & APPLICATIONS

The Tiny Jack (TJ) Series of 1/4" phone jacks features a slim design with a high packing density. It features black, plastic housing with a fully threaded nose. The TJ Series provides a Normally Closed switch design which makes them a perfect solution for design-in applications where the termination method is to a printed circuit board. The compact form factor of these connectors makes them perfect for situations where space saving is a priority or space for a connector is limited. Fits a 11.2mm chassis cutout.

Available in Mono-Switched (IO-TJ4HF) and Stereo-Switched (IO-TJ6HF) options for horizontal PCB mounting.

Also available with a half threaded nose (IO-TJ4HH & IO-TJ6HH).

PART NUMBER BREAKDOWN:

IO-**TJ**6HH
Series Identifier

IO-TJ**6**HH
Number of Pins

IO-TJ6**H**H
H = Horizontal PCB Mount

IO-TJ6H**H**
H = Half Threaded Nose
F - Full Threaded Nose

STANDARDS & CLASSIFICATIONS



Product specifications may change without prior notification

Io Audio Technologies® is a registered trademark of Knight Electronics, Inc.

10557 Metric Dr. Dallas

, TX 75243 | 214-340-0265 | 800-323-2439 | Fax: 214-340-5870 |

www.ioaudiotechologies.com