

93 Piece PRO Tool Set

With XXL3 rolling tool case

wiha 
Tools that work for you



**NO HASSLE
GUARANTEE**



Rugged Durability

Large capacity with over 100 tool compartments and robust construction for heavy everyday use



Easy Transport

Go anywhere with a 42-inch extendable handle and extra-large wheels to traverse stairs and rough terrain



Solid Stability

Fold the legs out for a stable step-stool, seat, or elevated work-station and strain-free removal of tools

93 Piece PRO Tool Set

With XXL3 rolling tool case



Tools that work for you

The 93 piece XXL3 PRO tool set includes a comprehensive set of “Wiha Pro-customer favorites” to build a high-value professional tool set ready to work for you

SKU: 91515

Rugged Durability

Large capacity with over 100 tool compartments and robust construction for heavy everyday use

Easy Transport

Go anywhere with a 42-inch extendable handle and extra-large wheels to traverse stairs and rough terrain

Solid Stability

Fold the legs out for a stable step-stool, seat, or elevated work-station and strain-free removal of tools



Remove up to two internal panels for expandable capacity



Easily configured versatile storage for hand tools, portable power tools & assorted components



Tools in this photo not included



Top & side grab handles for one or two-handed lifting & carrying



Extendable handle to 42-in for effortless rolling transport



Water-resistant lid seal for safe storage and protection



Fold-out legs for a stable step-stool, seat or elevated work-station



Slide-out step for a stable and convenient step-ladder configuration



V-channels with inch & metric rulers for on the spot cutting

Tools in this set include

35 PC. 1/4" RATCHET BIT SET

SLT 5.5MM | 6.5MM PH #0 | #1 | #2 | #3 SQ #1 | #2
TORX T8 | T10 | T15 | T20 | T25 | T27 | T30
HEX INCH 1/16 | 5/64 | 3/32 | 7/64 | 1/8 | 9/64
5/32 | 3/16 | 7/32 | 1/4"
HEX METRIC 1.5 | 2.0 | 2.5 | 3.0 | 4.0 | 5.0 | 6.0MM
1/4" BIT HOLDER AND 1/4" SOCKET ADAPTER

BITBUDDY TERMINATOR IMPACT BIT SET

PH #2 (2) SQ #2 (2) TORX T25 (2) | T30 (1)

14 IN ONE SOFTFINISH® STUBBY MULTI-BIT HOLDER

SLT 3.0+4.5 | 4.0+6.0 | 5.5+6.5MM
PH #0+3 | #1+2 SQ #0+3 | #1+2

SOFTFINISH® 11-IN-1 MULTI-DRIVER

SLT 1/4" | 3/16" PH #1 | #2 SQ #1 | #2
TORX T20 | T25 NUT DRIVER 1/4" | 5/16" | 3/8"

PICOFINISH® PRECISION SCREWDRIVERS

SLT 1.5 | 2.5 | 3.5MM PH #0 | #1

SOFTFINISH® SCREWDRIVERS

SLT 6.5MM SQ #2

EXTRA HEAVY DUTY SOFTFINISH® SCREWDRIVERS

SLT 8.0 | 12.0MM PH #2

8" HIGH LEVERAGE END CUTTING NIPPERS

8.0" | 200MM

AUTO GRIP PLIERS

10.0" | 250MM

BICUT SUPERCUT CUTTERS

8.0" | 200MM

LONG NOSE PLIERS WITH CUTTERS

8.0" | 200MM

COLOR CODED NUT SETTERS

1/4 | 5/16 | 3/8 | 7/16 | 1/2 | 9/16"

13 PC MAGICRING® HEX L-KEY SET

.050 | 1/16 | 5/64 | 3/32 | 7/64 | 1/8
9/64 | 5/32 | 3/16 | 7/32 | 1/4 | 5/16 | 3/8"

9 PC MAGICRING® HEX L-KEY SET

1.5 | 2.0 | 2.5 | 3.0 | 4.0 | 5.0 | 6.0 | 8.0 | 10.0MM

93 Piece PRO Tool Set :



Weight (lbs)	49.6500
RoHS Compliant	Yes
Head Type	slotted, phillips, square, torx, hex inch/metric nut driver, nut setters
Pieces In Set	93
UPC Code	084705915678
UNSPSC	27113201
Shipping Box	20.6 x 17 x 27.3