

USB-C Headphone Splitter, USB Type C Dual Headset Adapter w/Mic Input, USB C to 3.5mm Audio Adapter/Earphone Dongle, USB C to Audio Jack/Aux Output, 24-bit DAC

**Product ID:** USBC-AUDIO-SPLITTER



This USB Type-C Headphone Splitter enables two 3.5mm audio connections. The 3.5mm ports accept 4-pole 3.5mm TRRS connectors and support simultaneous stereo audio output and headset/microphone input. The adapter also features an integrated 2.75in (7cm) USB-C cable.

Connect two headsets to the same USB-C port. Microphone input is supported across both headsets, offering a convenient solution for team training and conferencing calls. The adapter supports dual CTIA or dual OMTP headset types allowing universal compatibility.

The USB-C headset dongle features built-in 24-bit Digital to Analog Converter (DAC). The DAC supports a sampling rate of up to 192kHz for uncompromising quality and performance.

The USB-C to dual-audio adapter is small and lightweight, perfect for professionals who are frequently on the go. It is the ideal solution for adding two 3.5mm audio jacks to a USB-C device.

This product is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance.

## Certifications, Reports and Compatibility



## Applications

## Features

- **USB-C HEADPHONE SPLITTER:** Convert the USB C port on laptop/phone/tablet into two 3.5mm headphone jacks for high quality audio, mic and headset controls on both 3.5mm jacks; Ideal for team conferencing/meetings/presentations/training centers
- **HIGH PERFORMANCE:** USBC to dual-headphones dongle features built-in 24-bit Digital to Analog Converter (DAC) ensuring uncompromising quality and performance for Hi-Res audio with sampling rate up to 192kHz
- **COMPATIBILITY:** The USB Type-C audio adapter supports dual CTIA or dual OMTP headphones/headsets; Compatible with MacBook Pro/MacBook/MacBook Air/iPad/iPad Pro/iPad Air/Samsung Galaxy S/Galaxy Note/Google Pixel; Ideal use with high impedance headsets
- **COMPACT DESIGN:** The AUX adapter is compact and lightweight and features an attached 2.7in/7cm cable with strain relief for portability and flexibility
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB Type C earphone splitter is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | 2 Years                        |
| Ports                 | 2                              |
| Connector Plating     | Aluminum                       |
| Cable Jacket Material | TPE - Thermoplastic Elastomers |

---

#### Performance

|                      |                                             |
|----------------------|---------------------------------------------|
| Audio Specifications | 16-bit depth at a sampling rate of 8~192kHz |
|                      | 24-bit depth at a sampling rate of 8~192kHz |

---

#### Connector(s)

|             |                                           |
|-------------|-------------------------------------------|
| Connector A | 1 - USB Type-C (24-pin) USB 2.0 (480Mbps) |
| Connector B | 2 - 3.5 mm Audio                          |

---

#### Environmental

|                       |                         |
|-----------------------|-------------------------|
| Operating Temperature | 0 to 70C (32 to 158F)   |
| Storage Temperature   | -10 to 70C (14 to 158F) |
| Humidity              | 5 to 90% RH             |

---

#### Physical Characteristics

|       |                    |
|-------|--------------------|
| Color | Black & Space Gray |
|-------|--------------------|

|                   |                  |
|-------------------|------------------|
| Connector Style   | Straight         |
| Material          | Aluminum         |
| Cable Length      | 0.3 in [0.7 cm]  |
| Cable OD          | 0.1 in [3.2 mm]  |
| Product Length    | 4.5 in [11.4 cm] |
| Product Width     | 1.1 in [2.7 cm]  |
| Product Height    | 0.3 in [8.0 mm]  |
| Weight of Product | 0.7 oz [19.0 g]  |

---

#### Packaging Information

|                           |                  |
|---------------------------|------------------|
| Package Quantity          | 1                |
| Package Length            | 3.5 in [9.0 cm]  |
| Package Width             | 4.9 in [12.5 cm] |
| Package Height            | 0.3 in [8.2 mm]  |
| Shipping (Package) Weight | 0.7 oz [20.0 g]  |

---

#### What's in the Box

|                     |                                          |
|---------------------|------------------------------------------|
| Included in Package | 1 - USB Type-C to 2x 3.5mm Audio Adapter |
|---------------------|------------------------------------------|

---

***\*Product appearance and specifications are subject to change without notice.***

