

EKDMGN08B-KIT:**Power Inductors for DC-DC Converter Circuit:**

No.	QTY	MANUFACTURER'S PART NUMBER	Product Description	DESCRIPTION
1	10	LQH3NPN1R0MMEL	Fixed IND SMD	Fixed IND 1uH 3000mA NONAUTO
2	10	LQH3NPN2R2MMEL	Fixed IND SMD	Fixed IND 2.2uH 2100mA NONAUTO
3	10	LQH3NPN3R3MMEL	Fixed IND SMD	Fixed IND 3.3uH 1900mA NONAUTO
4	10	LQH3NPN4R7MMEL	Fixed IND SMD	Fixed IND 4.7uH 1700mA NONAUTO
5	10	LQH3NPN6R8MMEL	Fixed IND SMD	Fixed IND 6.8uH 1450mA NONAUTO
6	10	LQH3NPN100MMEL	Fixed IND SMD	Fixed IND 10uH 1280mA NONAUTO
7	10	LQH3NPN150MMEL	Fixed IND SMD	Fixed IND 15uH 1020mA NONAUTO
8	10	LQH3NPN220MMEL	Fixed IND SMD	Fixed IND 22uH 860mA NONAUTO
9	10	LQH3NPN330MMEL	Fixed IND SMD	Fixed IND 33uH 760mA NONAUTO
10	10	LQH3NPN470MMEL	Fixed IND SMD	Fixed IND 47uH 610mA NONAUTO
11	10	LQH3NPN101MMEL	Fixed IND SMD	Fixed IND 100uH 430mA NONAUTO
12	10	LQH3NPNR68NJRL	Fixed IND SMD	Fixed IND 0.68uH 2860mA NONAUTO
13	10	LQH3NPN1R0MJRL	Fixed IND SMD	Fixed IND 1uH 2780mA NONAUTO
14	10	LQH3NPN2R2MJRL	Fixed IND SMD	Fixed IND 2.2uH 2200mA NONAUTO
15	10	LQH3NPN4R7MJRL	Fixed IND SMD	Fixed IND 4.7uH 1580mA NONAUTO
16	10	LQH3NPN100MJRL	Fixed IND SMD	Fixed IND 10uH 1200mA NONAUTO
17	10	LQH3NPN220MJRL	Fixed IND SMD	Fixed IND 22uH 800mA NONAUTO
18	10	LQH3NPN470MJRL	Fixed IND SMD	Fixed IND 47uH 570mA NONAUTO
19	10	LQH32PNR47NNCL	Fixed IND SMD	Fixed IND 0.47uH 4400mA NONAUTO
20	10	LQH32PN1R0NNCL	Fixed IND SMD	Fixed IND 1uH 3000mA NONAUTO
21	10	LQH32PN2R2NNCL	Fixed IND SMD	Fixed IND 2.2uH 2000mA NONAUTO
22	10	LQH32PN4R7NNCL	Fixed IND SMD	Fixed IND 4.7uH 1600mA NONAUTO
23	10	LQH32PN100MNCL	Fixed IND SMD	Fixed IND 10uH 1000mA NONAUTO
24	10	LQH32PN220MNCL	Fixed IND SMD	Fixed IND 22uH 650mA NONAUTO
25	10	LQH5BPNR47NT0L	Fixed IND SMD	Fixed IND 0.47uH 7.7A NONAUTO
26	10	LQH5BPN1R0NT0L	Fixed IND SMD	Fixed IND 1uH 5.8A NONAUTO
27	10	LQH5BPN2R2NT0L	Fixed IND SMD	Fixed IND 2.2uH 4A NONAUTO
28	10	LQH5BPN4R7NT0L	Fixed IND SMD	Fixed IND 4.7uH 3A NONAUTO
29	10	LQH5BPN100MT0L	Fixed IND SMD	Fixed IND 10uH 2A NONAUTO
30	10	LQH5BPN220MT0L	Fixed IND SMD	Fixed IND 22uH 1.4A NONAUTO