

SPARE PARTS LIST

MODEL NO. 8434D

ITEM	PART NO.	DESCRIPTION	QTY	NOTE
001	861583-3	NAME PLATE 8434D	1	
002	183845-2	HOUSING SET 6339D	1	
		INC. 24		
003	266130-9	*TAPPING SCREW BIND 3X 16 10PK6313DW	9	
004	344391-2	BIT HOLDER 6313DW/8413D-43D	1	
005	125316-3	SPEED CHANGE LEVER ASSY BHP451BDF451	1	
006	418753-1	F/R CHANGE LEVER 6319/6339/634	1	
007	263024-9	RUBBER PIN 4 6918D/6990D/6908	1	
008	650559-3	SWITCH C3LA-2A-ED 6319/6349/63	1	
009	687085-9	HOLDER 6313DW/8413D-43D/UB120D	1	
010	654168-0	SPRING TERMIANL (+) 6313DW/8418413-43D	1	
011	654169-8	SPRING TERMINAL (-) 6313D/SC16	1	
012	251464-3	*SPECIAL BOLT M6X22 LTH 5PK	1	
013	763188-4	KEYLESS DRILL CHUCK 13 6319/6339/6349	1	
014	253798-0	*THIN BLUE WASHER 13 5PK HP2010N	1	
015	125339-1	GEAR ASS'Y	1	
016	638376-1	YOKE UNIT 6319/6339/6349D	1	
017	629829-1	ARMATURE 6339	1	
018	638375-3	ENDBELL COMP 6319/6339/6349	1	
019	191971-3	CARBON BRUSH SET CB-430 8413D-43D/6317-47D	1	
020	643929-3	HOLDER CAP 6313DW/8413D/8433D	2	
021	266282-6	*TAPPING SCREW ST3x10 10PK	1	
022	689136-4	FELT SPACER 6319/6339/6349	1	
023	266045-0	*PT SCREW 4X20 TRILOBULAR 10PK	4	
024	183845-2	HOUSING SET 6339D	1	
		INC. 2		
025	232220-0	LEAF SPRING 6319/6339/6349	2	
026	819001-5	MAKITA LABEL	1	
027	263024-9	RUBBER PIN 4 6918D/6990D/6908	1	
028	344391-2	BIT HOLDER 6313DW/8413D-43D	1	
A01	122576-8	STOPPER POLE ASSY 6343DW/8413DBHP451	1	
A02	122711-8	GRIP ASSY 8414/8434/8444D	1	
A03	414938-7	BATTERY COVER UC120DW/VR250DW 5093DW/LS800DWB	3	
A05	193060-0	BATTERY 1435 14V 3.0AH Ni-MH	2	
A06	784637-8	*45mm DOUBLE-END PH 2 x SLOT 6	2	
A07	824626-2	PLASTIC CASE 8414/34/44/6336	1	
A08	192752-8	ML140 RECHARGEABLE FLASHLIGHT	1	
A09	345261-8	HOOK BUTTON ML702/902/903/180	2	
A10	417926-3	STRAP ML702/902/903/180	1	

SERVICE DRAWING

MODEL NO. 8434D

