

Hot air tool

HL 2020 E -240V

UK Folding box
EAN 4007841 009656
Article number 009656



Function description

The master class. Electronically controlled hot air tool HL 2020 E with LCD. Professional technology for shaping tiles, de-soldering circuit boards, welding plastics, drying repair filler, shrinking cable sleeves, soldering pipes and a whole lot more. Adjustable by joystick from 80°C to 630°C in 10°C steps. Residual heat indicator to prevent burns.

Technical specifications

Temperature	80 – 630 °C	Function, hanger	Yes
Airflow rate	150 – 500 l/min	Restart protection	No
Temperature setting	in 10°C steps by joystick	Temperature scanner	Yes
Settings made via	joystick	Fine dust filter	No
Temperature display	LCD display	Thermal cut-out	Yes
Airflow control	Settings	Thermostat	Yes
Programming function	No	Cord length	2.2 m
Residual heat indicator	Yes	Dimensions (L x W x H)	253 x 86 x 200 mm
Motor, type	Brush motor	PU1, net weight	0,88 kg
Heating element	Ceramic heating element	Manufacturer's Warranty	3 years
Mains power supply	220 – 230 V / 50 – 60 Hz	PU1, EAN	4007841009656

Accessories

EAN 4007841 014919	Temperature scanner HL Scan
EAN 4007841 078218	Fine dust filter HL 1920 E - HG 2320 E
EAN 4007841 009625	HL Light
EAN 4007841 010317	Paint Scraper Set
EAN 4007841 074210	ABS plastic welding rod
EAN 4007841 073411	PP plastic welding rod
EAN 4007841 071219	HDPE plastic welding rod

Hot air tool

HL 2020 E -240V

UK Folding box

EAN 4007841 009656

Article number 009656



Accessories

EAN 4007841 073114	PVC plastic welding rod
EAN 4007841 006648	Crimp connectors - Ø 1.5 - 2.5 mm
EAN 4007841 072766	Shrink tubing III - Ø 4,8 - 12,0 mm
EAN 4007841 006662	Crimp connectors - Ø 0.1 - 6.0 mm
EAN 4007841 071318	Shrink tubing I - Ø 1,6 - 4,8 mm
EAN 4007841 006655	Crimp connectors - Ø 0.5 - 1.5 mm
EAN 4007841 070717	Reduction nozzle 14 mm
EAN 4007841 074715	Wide-slit nozzle
EAN 4007841 012311	Feed roller
EAN 4007841 071417	Shrink tubing II - Ø 4,8 - 9,5 mm
EAN 4007841 070212	Surface nozzle 75 mm
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 070915	Welding nozzle
EAN 4007841 070113	Surface nozzle 50 mm
EAN 4007841 070311	Window nozzle 50 mm
EAN 4007841 070519	Reflector nozzle
EAN 4007841 070410	Window nozzle 75 mm
EAN 4007841 074616	Soldering reflector nozzle 10 mm
EAN 4007841 034566	HL Tool Stand
EAN 4007841 070618	Reduction nozzle 9 mm